



Technical drawing of a rectangular plate with dimensions and tolerances:

- Overall width: $G \begin{smallmatrix} +0.05 \\ 0 \end{smallmatrix}$
- Overall height: $F \begin{smallmatrix} 0 \\ -0.05 \end{smallmatrix}$
- Distance between vertical centerlines: $C \pm 0.02$
- Distance between horizontal centerlines: $P = 0.4 \pm 0.02$
- Distance from top edge to first vertical centerline: $0.8 \begin{smallmatrix} 0 \\ -0.05 \end{smallmatrix}$
- Distance from bottom edge to first vertical centerline: $1.98 \begin{smallmatrix} +0.05 \\ 0 \end{smallmatrix}$
- Distance from right edge to last vertical centerline: $1.28 \begin{smallmatrix} 0 \\ -0.05 \end{smallmatrix}$
- Distance from right edge to last horizontal centerline: $2.76 \begin{smallmatrix} +0.05 \\ 0 \end{smallmatrix}$
- Distance between vertical centerlines (bottom): 0.23 ± 0.02

A—A

ENGAGEMENT FIGURE



5 METAL HOLD DOWN PLATING SPECIFICATIONS.
MOUNTING AREA: GOLD 0.05μm MIN.
UNDERPLATING : NICKEL 1μm MIN.

6. PEEL FORCE OF COVER TAPE REFERS TO JIS C 0806.

7 PLEASE CONTACT US IN CASE YOU WILL MAKE
DIFFERENT SETTINGS FROM OUR RECOMMENDATION.

4 CONTACT PLATING SPECIFICATIONS.

CONTACT AREA : GOLD 0.1 μ m MIN.

SMT LEAD : GOLD 0.05 μ m MIN.

UNDERPLATING : NICKEL 1 μ m MIN.


(SURFACE : SEALING)

PART No.	CODE No.	B	C	D	E	F	G
BM10B(0.8)-10DP-0.4V(75)	CL684-6007-5-75	3.32	1.6	0.8	2.74	2.3	3.18
BM10B(0.8)-16DP-0.4V(75)	CL684-6047-0-75	4.52	2.8	1.6	3.94	3.5	4.38
BM10B(0.8)-20DP-0.4V(75)	CL684-6009-0-75	5.32	3.6	1.6	4.74	4.3	5.18
BM10B(0.8)-24DP-0.4V(75)	CL684-6011-2-75	6.12	4.4	2.0	5.54	5.1	5.98
BM10B(0.8)-30DP-0.4V(75)	CL684-6013-8-75	7.32	5.6	2.0	6.74	6.3	7.18
BM10B(0.8)-34DP-0.4V(75)	CL684-6015-3-75	8.12	6.4	2.4	7.54	7.1	7.98
BM10B(0.8)-40DP-0.4V(75)	CL684-6003-4-75	9.32	7.6	2.4	8.74	8.3	9.18
BM10B(0.8)-44DP-0.4V(75)	CL684-6039-1-75	10.12	8.4	2.8	9.54	9.1	9.98
BM10B(0.8)-50DP-0.4V(75)	CL684-6017-9-75	11.32	9.6	2.8	10.74	10.3	11.18
BM10B(0.8)-60DP-0.4V(75)	CL684-6001-9-75	13.32	11.6	3.2	12.74	12.3	13.18

3	PHOSPHOR BRONZE	5	5	PS	PLASTIC REEL (BLACK)	
2	PHOSPHOR BRONZE	4	5	POLYESTER	CLEAR (COVER TAPE)	
1	LCP	UL94V-0. BLACK		4	PS	CLEAR (EMBOSSED CARRIER TAPE)
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 10 : 1		COUNT 4	DESCRIPTION OF REVISIONS DIS-H-005402	DESIGNED KR. AJITO	CHECKED TS. MIYAZAKI	DATE 10. 12. 16
-------------	--	-----------------	--	------------	--	-----------------------	-------------------------	--------------------

HIROSE ELECTRIC CO., LTD.	APPROVED : KH. IKEDA	09. 06. 23	DRAWING NO.	EDC3-317902-75
	CHECED : TS. MIYAZAKI	09. 06. 23	PART NO.	BM10B<0. 8> - * DP-0. 4V<75>
	DESIGNED : NY. YAMASHIRO	09. 06. 23	CODE NO.	CL684-****-* -75
	DRAWN : NY. YAMASHIRO	09. 06. 23		



PART No.	CODE No.	K	L	M	N
BM10B(0.8)-10DP-0.4V(75)	CL684-6007-5-75	12	5.5	13.5	17.5
BM10B(0.8)-16DP-0.4V(75)	CL684-6047-0-75	16	7.5	17.5	21.5
BM10B(0.8)-20DP-0.4V(75)	CL684-6009-0-75	16	7.5	17.5	21.5
BM10B(0.8)-24DP-0.4V(75)	CL684-6011-2-75	16	7.5	17.5	21.5
BM10B(0.8)-30DP-0.4V(75)	CL684-6013-8-75	16	7.5	17.5	21.5
BM10B(0.8)-34DP-0.4V(75)	CL684-6015-3-75	16	7.5	17.5	21.5
BM10B(0.8)-40DP-0.4V(75)	CL684-6003-4-75	24	11.5	25.5	29.5
BM10B(0.8)-44DP-0.4V(75)	CL684-6039-1-75	24	11.5	25.5	29.5
BM10B(0.8)-50DP-0.4V(75)	CL684-6017-9-75	24	11.5	25.5	29.5
BM10B(0.8)-60DP-0.4V(75)	CL684-6001-9-75	24	11.5	25.5	29.5

HRS	DRAWING NO. EDC3-317902-75	
	PART NO. BM10B(0.8)*DP-0.4V(75)	
	CODE NO. CL684-*****-75	2 2