






- NOTE 1. ALL LEAD CO-PLANARITY SHALL BE 0.08mm MAX
2. CONTACT PLATING SPECIFICATIONS
CONTACT AREA : GOLD $0.05 \mu\text{m}$ MIN
SMT LEAD : GOLD $0.05 \mu\text{m}$ MIN
UNDERPLATING : NICKEL $1 \mu\text{m}$ MIN
(SURFACE : SEALING)
3. METAL FITTING PLATING SPECIFICATIONS
SMT LEAD : GOLD $0.05 \mu\text{m}$ MIN
UNDERPLATING : NICKEL $1 \mu\text{m}$ MIN
(SURFACE : SEALING)
4. HRS MARK AND CAV NO. ARE INDICATED IN APPROX POSITION SHOWN.
5. GATE POSITION IS INDICATED IN APPROX POSITION SHOWN.



ENGAGEMENT FIGURE (50:1)




4	PS	CLEAR (EMBOSSED CARRIER TAPE)		7	PS	CLEAR (REINFORCEMENT COLLAR)
3	BRASS	3		6	PS	BLACK (PLASTIC REEL)
2	PHOSPHOR BRONZE	2		5	POLYESTER	CLEAR (COVER TAPE)
1	LCP	UL94 V-0, BLACK				
NO.	MATERIAL	FINISH , REMARKS		NO.	MATERIAL	FINISH , REMARKS

UNITS mm		SCALE 10 : 1	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
HRS HIROSE ELECTRIC CO., LTD.		APPROVED : KH. IKEDA	12.03.02	DRAWING NO. EDC3-332315-01			
		CHECKED : TS. MIYAZAKI	12.03.02	PART NO. BM20B(0.8)-20DS-0.4V(51)			
		DESIGNED : YK. SATAKE	12.03.02	CODE NO. CL684-9009-7-51			
		DRAWN : KR. AJITO	11.11.02				
				1/3			


May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

◆RECOMMENDED PCB LAYOUT




◆RECOMMENDED METAL MASK DIMENSIONS

MATAL MASK THICKNESS : $100 \mu\text{m}$



6 RECOMMENDED REFLOW TEMPERATURE PROFILE USING LEAD-FREE SOLDER PASTE.



- REFLOW METHOD : IR REFLOW
NUMBER OF REFLOW CYCLES : 2 CYCLES MAX.
- 1) REFLOW TIME
DURATION ABOVE 220°C. 60 SEC MAX.
(PEAK TEMPERATURE : 250°C MAX)
 - 2) PRE-HEAT TIME
PRE-HEAT TEMPERATURE(MIN): 150°C
PRE-HEAT TEMPERATURE(MAX): 180°C
PRE-HEAT TIME: 90-120 SEC.

6 THE TEMPERATURE PROFILE IS PER THE CONDITIONS SHOWN ABOVE.
ADDITIONAL FACTORS, SUCH AS SOLDER PASTE TYPE, PCB SIZE AND
OTHER MOUNTED COMPONENTS COULD AFFECT THE PROFILE. THEREFORE,
A THOROUGH EVALUATION OF MOUNTING CONDITION IS REQUIRED
PRIOR TO PRODUCTION. TEMPERATURE IS MEASURED AT CONTACT LEAD.

HRS

DRAWING NO.	EDC3-332315-01
PART NO.	BM20B(0.8)-20DS-0.4V(51)
CODE NO.	CL684-9009-7-51

2/3

