

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-40℃ TO +85℃	STORAGE TEMPERATURE RANGE	-25℃ TO +70℃ (AT PACKING)		
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS		QT AT
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		X X		
MARKING		CONFIRMED VISUALLY.		X ACCORDING TO DRAWING. X		
ENVIRONMENTAL CHARACTERISTICS						
WATER RESISTANCE (MATING)		PUT THE PRODUCT UNDER WATER FOR 1 min. WITH AIR PRESSURE 4.9kPa.(IP67).		NO AIR LEAKAGE		X -
COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED	DATE
REMARK			APPROVED	TS.YAMAZAKI	20190823	
			CHECKED	SJ.SUZUKI	20190823	
			DESIGNED	FS.YOSHIDA	20190823	
			DRAWN	SU.KURODA	20190823	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test	DRAWING NO.		ELC-176799-00-00			
HRS	SPECIFICATION SHEET		PART NO.	SW20-PC1		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL717-5500-0-00		1/1