





APPLICABLE STANDARD								
RATING	OPERATING TEMPERATURE RANGE	-40°C TO +85°C		STORAGE TEMPERATURE RANGE	-25°C TO +70°C (AT PACKING)			
	POWER	—w		CHARACTERISTIC IMPEDANCE				
SPECIFICATIONS								
ITEM		TEST METHOD			REQUIREMENTS		QT	AT
CONSTRUCTION								
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.		X	X
MARKING		CONFIRMED VISUALLY.					X	X
ENVIRONMENTAL CHARACTERISTICS								
WATER RESISTANCE (MATING) 		PUT THE PRODUCT UNDER WATER FOR 1 min. WITH AIR PRESSURE 4.9kPa.(IP67)			NO AIR LEAKAGE		X	-
COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED		DATE	
 1	DIS-K-00000296		FS. YOSHIDA		YY. HIYAMA		16. 06. 02	
REMARK					APPROVED	MT. SHIBUTANI	10. 06. 24	
					CHECKED	YH. MASUZAKI	10. 06. 23	
					DESIGNED	SI. MATSUMOTO	10. 06. 23	
					DRAWN	SI. MATSUMOTO	10. 06. 23	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-176920-00			
	SPECIFICATION SHEET		PART NO.		SW20-RC2			
	HIROSE ELECTRIC CO., LTD.		CODE NO.		CL717-5503-8-00			1/1