








Apr.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO +125 °C	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C ⁽¹⁾
	VOLTAGE	 60 V AC/DC	STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 85% MAX
	CURRENT	2 A		(NOT DEWED)
SPECIFICATIONS				
ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	x	x
MARKING	CONFIRMED VISUALLY.		x	x
ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	1A DC.	8 mΩ MAX.	-	-
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20 mV AC MAX, 0.1 mA(DC OR 1000Hz)	8 mΩ MAX.	-	-
INSULATION RESISTANCE	500V DC.	100 MΩ MIN.	x	-
VOLTAGE PROOF	1000 V AC FOR 1 min.	 NO BREAKDOWN.	-	-
MECHANICAL CHARACTERISTICS				
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 16 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
VIBRATION	FREQUENCY 20 TO 200Hz (88m/s ²) SWEEP TIME 3min.(ROUND TRIP) AT 3h FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 7ΩMIN, 1μs MIN. ② CONTACT RESISTANCE: 16 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
SHOCK	981m/s ² DURATION OF PULSE 6ms AT 3 TIMES FOR 6 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 7ΩMIN, 1μs MIN. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
LOCK STRENGTH	MEASURE BREAK STRENGTH OF THE LOCK BY PULLING THE CONNECTOR IN THE MATING DIRECTION.	100N MIN.	x	-
ENVIRONMENTAL CHARACTERISTICS				
DAMP HEAT (STEADY STATE)	EXPOSED AT 60 °C, 90 ~ 95 %, 96 h.	① CONTACT RESISTANCE: 16 mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
RAPID CHANGE OF TEMPERATURE	TEMPERATURE- 40 →ROOM TEMP →125°C→ ROOM TEMP TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.	① CONTACT RESISTANCE: 16 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
DRY HEAT	EXPOSED AT 140°C, 120 h.	① CONTACT RESISTANCE: 16 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
COLD	EXPOSED AT -40°C, 120 h.	① CONTACT RESISTANCE: 16 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	-	-
RESISTANCE TO SO ₂ GAS	EXPOSED IN 25 PPM AT 75% MIN FOR 96h.	CONTACT RESISTANCE: 16 mΩ MAX.	-	-
RESISTANCE TO HIGH-PRESSURE WASHING 	AFTER HEATING AT 120°C FOR 120 h, WATER AT 80°C, 10 MPa, FOR 30 sec AT THE POSITIONS OF ① TO ④. ROTATE THE MOUNTING BASE AT 5 r/min. 	① NO WATER PENETRATION PERMITTED. ② INSULATION RESISTANCE:100 MΩ MIN.	x	-
COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 3	DIS-T-00005917	AN. SAIKI	HH. TSUKUMO	20200312
REMARK		APPROVED	HK. UMEHARA	20190207
(NOTE1) "STORAGE" means a long-term storage state for the unused product.		CHECKED	HH. TSUKUMO	20190207
		DESIGNED	AS. SHIBAHARA	20190207
		DRAWN	GYEONGMIN LEE	20190207
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC-378451-00-00	
	SPECIFICATION SHEET	PART NO.	ZE064W-14DS-HU/R (B)	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL753-2011-0-00	 1/1