

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-35°C TO +85°C(NOTE 1)	STORAGE TEMPERATURE RANGE	-10°C TO +60°C (NOTE 3)	
	OPERATING HUMIDITY RANGE	40% TO 80% (NOTE 2)	STORAGE HUMIDITY RANGE	40% TO 70% (NOTE 3)	
	VOLTAGE	100 V AC/DC	APPLICABLE CONNECTOR	DF19#-20P-1H(##) DF19-20P-1V(##)	
	CURRENT	0.5 A/pin			
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	QTAT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	XX
MARKING		CONFIRMED VISUALLY.			XX
REMARKS					
<p>NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT.</p> <p>NOTE2: NO CONDENSING.</p> <p>NOTE3: APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFORE ASSEMBLY. AFTER ASSEMBLY, OPERATING TEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERIM STORAGE DURING TRANSPORTATION.</p>					
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
Unless otherwise specified, refer to IEC 60512.			APPROVED	HS. OKAWA	20200331
			CHECKED	TS. KUMAZAWA	20200331
			DESIGNED	HK. HAYASHI	20200331
			DRAWN	DS. HIROWATARI	20200316
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-162455-06-00
	SPECIFICATION SHEET		PART NO.	DF19G-20S-1F-GND (06)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL685-0010-3-06	1/1