





May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

ELV. RoHS COMPLIANT




Mated connectors



NOTES


- Recommended reflow profile (See right graph)
Cycle time : Twice
Peak temperature : 250°C
230°C MIN : 30~60s
Preheating area : 130~180°C, 60~120s
- Hand soldering : 280~300°C 2s Max
- Recommended thickness of PCB : 1.6^{+0.2}₀mm
- Recommended thickness of Soldering paste : 0.15mm




3	Brass	Tin plating	5	Copper alloy	Tin plating
2	PA	Black	4	PA	Purple
1	Brass	Tin plating			
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 2	DESCRIPTION OF REVISIONS DIS-T-00003144	DESIGNED NK. IKUTA
HIROSE ELECTRIC CO., LTD.				CHECKED KI. HIROKAWA	17.06.30
				DESIGNED NK. IKUTA	17.06.30
				DRAWN GYEONGMIN LEE	17.06.30
				DRAWING NO. EDC-377154-00-00	
				PART NO. GT43-1P-H(F)	
				CODE NO. CL753-1017-0-00	
					1/2

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

tray A(1:2)




tray B(1:2)



Packing style

- ①Put the connector on the tray A and tray B.
- ②Stac tray A and tray B staggered. Top tray is empty.
1tray : 70pcs
- ③Put two sets of cardboard.
Cardboard : 700pcs



HRS

DRAWING NO.	EDC-377154-00-00
PART NO.	GT43-1P-H(F)
CODE NO.	CL753-1017-0-00

1/2