
Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO +125 °C	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C (1)
	VOLTAGE	1 60 V AC/DC	STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 85% MAX (NOT DEWED)
	CURRENT	2 A		

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	×	×
MARKING	CONFIRMED VISUALLY.		×	×
ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	1A DC.	8 mΩ MAX .	—	—
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20 mV AC MAX, 0.1 mA(DC OR 1000Hz)	8 mΩ MAX .	—	—
INSULATION RESISTANCE	500V DC.	100 MΩMIN.	×	—
VOLTAGE PROOF	1000 V AC FOR 1 min. 1	NO BREAKDOWN.	—	—
MECHANICAL CHARACTERISTICS				
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 16 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— ×	— —
VIBRATION	FREQUENCY 20 TO 200Hz (88m/s²) SWEEP TIME 3min.(ROUND TRIP) AT 3h FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 7ΩMIN, 1μs MIN. ② CONTACT RESISTANCE: 16 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— — ×	— — —
SHOCK	981m/s² DURATION OF PULSE 6ms AT 3 TIMES FOR 6 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 7ΩMIN, 1μs MIN. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— ×	— —
LOCK STRENGTH	MEASURE BREAK STRENGTH OF THE LOCK BY PULLING THE CONNECTOR IN THE MATING DIRECTION.	100N MIN.	×	—
ENVIRONMENTAL CHARACTERISTICS				
DAMP HEAT (STEADY STATE)	EXPOSED AT 60 °C, 90 ～ 95 %, 96 h.	① CONTACT RESISTANCE: 16 mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— × ×	— — —
RAPID CHANGE OF TEMPERATURE	TEMPERATURE- 40 →ROOM TEMP →125°C→ ROOM TEMP TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.	① CONTACT RESISTANCE: 16 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— ×	— —
DRY HEAT	EXPOSED AT 140°C, 120 h.	① CONTACT RESISTANCE: 16 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— ×	— —
COLD	EXPOSED AT -40°C, 120 h.	① CONTACT RESISTANCE: 16 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— ×	— —
RESISTANCE TO SO_2 GAS	EXPOSED IN 25 PPM AT 75% MIN FOR 96h.	CONTACT RESISTANCE: 16 mΩ MAX.	—	—
RESISTANCE TO HIGH-PRESSURE WASHING 1	AFTER HEATING AT 120°C FOR 120 h, WATER AT 80°C, 10 MPa, FOR 30 sec AT THE POSITIONS OF ① TO ④. ROTATE THE MOUNTING BASE AT 5 r/min. 	① NO WATER PENETRATION PERMITTED. ② INSULATION RESISTANCE:100 MΩ MIN.	× ×	— —

	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
1	3	DIS-T-00005917	AN. SAIKI	HH. TSUKUMO	20200312

REMARK
(NOTE1) "STORAGE" means a long-term storage state for the unused product.

APPROVED	OM. MIYAMOTO	20190521
CHECKED	HH. TSUKUMO	20190521
DESIGNED	AS. SHIBAHARA	20190521
DRAWN	MINTAE KANG	20190521

Note QT:Qualification Test AT:Assurance Test X:Applicable Test

DRAWING NO. ELC-374260-00-00

HRS

SPECIFICATION SHEET

HIROSE ELECTRIC CO., LTD.

PART NO. ZE064W-24DS-HU/R(B)

CODE NO. CL753-2006-0-00 1 1/1

FORM HD0011-2-1