


APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO +125 °C	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C ⁽¹⁾	
	VOLTAGE	\triangle 60 V AC/DC	STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 85% MAX	
	CURRENT	2 A		(NOT DEWED)	
SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	x	x	
MARKING	CONFIRMED VISUALLY.		x	x	
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE	1A DC.	8 m Ω MAX.	—	—	
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20 mV AC MAX, 0.1 mA(DC OR 1000Hz)	8 m Ω MAX.	—	—	
INSULATION RESISTANCE	500V DC.	100 M Ω MIN.	x	—	
VOLTAGE PROOF	1000 V AC FOR 1 min.	\triangle NO BREAKDOWN.	—	—	
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 16 m Ω MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— x	— —	
VIBRATION	FREQUENCY 20 TO 200Hz (88m/s ²) SWEEP TIME 3min.(ROUND TRIP) AT 3h FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 7 Ω MIN, 1 μ s MIN. ② CONTACT RESISTANCE: 16 m Ω MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— — x	— — —	
SHOCK	981m/s ² DURATION OF PULSE 6ms AT 3 TIMES FOR 6 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 7 Ω MIN, 1 μ s MIN. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— x	— —	
LOCK STRENGTH	MEASURE BREAK STRENGTH OF THE LOCK BY PULLING THE CONNECTOR IN THE MATING DIRECTION.	100N MIN.	—	—	
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)	EXPOSED AT 60 °C, 90 ~ 95 %, 96 h.	① CONTACT RESISTANCE: 16 m Ω MAX. ② INSULATION RESISTANCE:100 M Ω MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— x x	— — —	
RAPID CHANGE OF TEMPERATURE	TEMPERATURE- 40 →ROOM TEMP →125°C→ ROOM TEMP TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.	① CONTACT RESISTANCE: 16 m Ω MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— x	— —	
DRY HEAT	EXPOSED AT 140°C, 120 h.	① CONTACT RESISTANCE: 16 m Ω MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— x	— —	
COLD	EXPOSED AT -40°C, 120 h.	① CONTACT RESISTANCE: 16 m Ω MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	— x	— —	
RESISTANCE TO SO ₂ GAS	EXPOSED IN 25 PPM AT 75% MIN FOR 96h.	CONTACT RESISTANCE: 16 m Ω MAX.	—	—	
RESISTANCE TO HIGH-PRESSURE WASHING \triangle 1	AFTER HEATING AT 120°C FOR 120 h, WATER AT 80°C, 10 MPa, FOR 30 sec AT THE POSITION OF ① TO ④. ROTATE THE MOUNTING BASE AT 5 r/min. 	① NO WATER PENETRATION PERMITTED. ② INSULATION RESISTANCE:100 M Ω MIN.	x x	— —	
COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
\triangle 3	DIS-T-00005917	AN. SAIKI	HH. TSUKUMO	20200312	
REMARK		APPROVED	AH. EDASHIGE	20190122	
(NOTE1) "STORAGE" means a long-term storage state for the unused product.		CHECKED	HH. TSUKUMO	20190122	
		DESIGNED	AS. SHIBAHARA	20190122	
		DRAWN	DS. HIROWATARI	20190122	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.		ELC-374261-00-00	
HRS	SPECIFICATION SHEET	PART NO.	ZE064W-WCP (2022)		
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL753-2007-0-00	\triangle	1/1