


1. Scope

This document specifies the crimp contact specification for
GT16G-/1.6-2.9SC (CL766-0024-8)

2. Applicable cable

Equivalent to 1.5D-2W

3. Specification



Items		Dimensions (mm)	Notes
Jacket position	A	0.3~0.9	
Outer conductor position	B	0.1~0.6	
bell-mouth	C1	—	
	C2	—	
bent-up	D	within 5°	
bent-down	E	within 5°	
twisting	F	within ±5°	
rolling	G	—	
lance height	H	—	
cut-off-tub	I	—	
strip length	J1	3.9~4.2	
	J2	0.5~0.8	
crimp burr height	K	—	

COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△				
名称 TITLE		HRS HIROSE ELECTRIC CO., LTD.		
Crimp contact specification for GT16G-/1.6-2.9SC		APPROVED	KI. HIROKAWA	17. 10. 03
		CHECKED	KI. HIROKAWA	17. 10. 03
		DESIGNED	KT. MAKI	17. 10. 03
		WRITTEN	MM. ARAKI	17. 10. 03
技術指定書 TECHICAL SPECIFICATION		ETAD-T0448-00		△ 1 / 1