

APPLICABLE STANDARD							
RATING	OPERATING TEMPERATURE RANGE	-30 °C TO +105 °C (NOTE1)		STORAGE TEMPERATURE RANGE	-40 °C TO +105 °C		
	VOLTAGE	250 V AC		CURRENT	1 A		
	CHARACTERISTIC IMPEDANCE	50 Ω					
SPECIFICATIONS							
ITEM		TEST METHOD		REQUIREMENTS		QT AT	
CONSTRUCTION							
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		×	×
MARKING		CONFIRMED VISUALLY.				×	×
ELECTRIC CHARACTERISTICS							
CONTACT RESISTANCE		1A DC.		30 mΩ MAX.		—	—
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD		20 mV AC MAX, 0.1 mA(OR 1kHz)		30 mΩ MAX.		—	—
INSULATION RESISTANCE		500 V DC		100 MΩ MIN.		×	—
VOLTAGE PROOF		650 V AC FOR 1 MIN.		NO FLASHOVER OR BREAKDOWN.		×	—
VOLTAGE STANDING WAVE RATIO		FREQUENCY 0 TO 6 GHz		VSWR 1.5 MAX.		×	—
MECHANICAL CHARACTERISTICS							
CONTACT INSERTION AND EXTRACTION FORCES		BY STEEL GAUGE.		INSERTION FORCE N MAX. WITHDRAWAL FORCE N MIN.		—	—
MECHANICAL OPERATION		30 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 60 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.		—	—
VIBRATION		FREQUENCY 20 TO 200 Hz, 43.1m/s ² , AT 3h FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② CONTACT RESISTANCE: 60 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.		—	—
SHOCK		FREQUENCY 20 TO 50 Hz,66.6m/ s ² AT 1 h.		① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② CONTACT RESISTANCE: 60 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.		—	—
LOCK STRENGTH		APPLYING A PULL FORCE THE MATING AXIALLY AT 98N MAX.		① DURING APPLYING,MATING COMPLETELY. ② AFTER APPLYING,NO DEFECT OF MATING PARTS.		×	—
ENVIRONMENTAL CHARACTERISTICS							
DAMP HEAT (STEADY STATE)		EXPOSED AT 60°C, 90 TO 95%, 500h.		① CONTACT RESISTANCE: 60 mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.		—	—
RAPID CHANGE OF TEMPERATURE		TEMPERATURE:-40→5 TO 35→85→5 TO 35°C TIME: 30→5→30→5 MIN UNDER 1000 CYCLES.		① CONTACT RESISTANCE: 60 mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.		×	—
DRY HEAT		EXPOSED AT 105°C, 300h.		① CONTACT RESISTANCE: 60 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.		—	—
COLD		EXPOSED AT -55°C, 120h.		① CONTACT RESISTANCE: 60 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.		×	—
RESISTANCE TO SO ₂ GAS		EXPOSED IN 500 PPM FOR 8h.		① CONTACT RESISTANCE: 60 mΩ MAX. ② NO HEAVY CORROSION.		—	—
RESISTANCE TO SOLDERING HEAT		TOP OF IRON 350°C, 10 SEC.		NO DEFORMATION IN CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.		—	—
SOLDERABILITY		TOP OF IRON 350°C, 3 SEC.		A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.		—	—
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED	DATE
△							
REMARK (NOTE1) INCLUDE THE TEMPERATURE RISING BY CURRENT.				APPROVED	NH. NAKATA	15. 08. 08	
				CHECKED	KI. HIROKAWA	15. 08. 07	
				DESIGNED	NK. IKUTA	15. 08. 07	
				DRAWN	NK. IKUTA	15. 08. 07	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.		ELC-165988-24-00	
HRS	SPECIFICATION SHEET			PART NO.	GT16G-1S-HU (24)		
	HIROSE ELECTRIC CO., LTD.			CODE NO.	CL766-0026-3-24 △ 1/1		