

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO 105 °C (NOTE1)		STORAGE TEMPERATURE RANGE	-40 °C TO 105 °C	
	VOLTAGE	250 V AC/DC		CURRENT	3 A	
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS		QT AT
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		X X
MARKING		CONFIRMED VISUALLY.				X X
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE		1A DC.		30 mΩ MAX.		X —
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD		20 mV AC MAX, 0.1 mA(DC OR 1000Hz)		30 mΩ MAX.		X —
INSULATION RESISTANCE		— V DC		1000 MΩ MIN.		— —
VOLTAGE PROOF		— V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.		— —
MECHANICAL CHARACTERISTICS						
CONTACT INSERTION AND EXTRACTION FORCE		MEASURING BY OPPOSITE CONTACT		INSERTION FORCE:4.9N MAX EXTRACTION FORCE:4.9N MAX		X — X —
MECHANICAL OPERATION		30 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 60 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		X — X —
VIBRATION		FREQUENCY 20 TO 400 Hz, 43.1 m/s <sup>2</sup> AT 3 h FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② CONTACT RESISTANCE: 60 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		X — X — X —
SHOCK		FREQUENCY 20 TO 50 Hz, 66.6 m/s <sup>2</sup> AT 1 h.		① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② CONTACT RESISTANCE: 60 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		X — X — X —
LOCK STRENGTH		APPLYING A PULL FORCE THE MATING AXIALLY AT —N MAX.		① DURING APPLYING,MATING COMPLETELY. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		— — — —
ENVIRONMENTAL CHARACTERISTICS						
DAMP HEAT (STEADY STATE)		EXPOSED AT 60 °C, 90 ~ 95 %, 500 h.		① CONTACT RESISTANCE: 60 mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		X — — — X —
THERMAL SHOCK		TEMPERATURE-40→5 TO 35→120→5 TO 35°C TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.		① CONTACT RESISTANCE: 60 mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		X — — — X —
DRY HEAT		EXPOSED AT 120°C, 300 h.		① CONTACT RESISTANCE: 60 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		X — X —
COLD		EXPOSED AT -40°C , 120 h.		① CONTACT RESISTANCE: 60 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		X — X —
RESISTANCE TO HSO <sub>3</sub> GAS		EXPOSED IN 500 PPM FOR 8h.		① CONTACT RESISTANCE: 60 mΩ MAX. ② NO HEAVY CORROSION.		X — X —
RESISTANCE TO SOLDERING HEAT		SPECIFIED TEMPERATURE PROFILE FOR 2CYCLES.		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.		— —
SOLDERABILITY		SOLDERED AT SPECIFIED TEMPERATURE PROFILE.		A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.		— —
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
△						
REMARK (NOTE1) INCLUDE THE TEMPERATURE RISING BY CURRENT.				APPROVED	HS. OZAWA	15. 03. 30
				CHECKED	HS. OZAWA	15. 03. 30
				DESIGNED	YT. HAYAKAWA	15. 03. 30
				DRAWN	YT. HAYAKAWA	15. 03. 30
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-168756-02-00	
HRS	SPECIFICATION SHEET		PART NO.	GT25H-2024SCF (02)		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL775-0039-6-02 △ 1/1		