







ELV, RoHS COMPLIANT



NOTE1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW (REFER TO RIGHT FIG.)
 USED REFLOW SYSTEM : IR IN THE AIR OR NITROGEN
 NO. OF CYCLES : 2 MAX
 PEAK : 250°C
 OVER 230°C : 20~40s
 PREHEAT : 150~180°C 60~120s
 2. TEMPERATURE FOR SOLDERING IRON : 280~300°C WITHIN 2s
 3. COPLANARITY SHALL BE 0.1mm MAX.
 4. RECOMMENDED PCB THICKNESS IS 1.6mm
 5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.




3	BRASS	TIN PLATED	6	PET			
2	BRASS	TIN PLATED	5	PS			
1	PA	BLACK	4	BRASS	TIN PLATED		
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS		
UNITS mm	⊙	SCALE 2 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-T-00006626	DESIGNED DONGCHAN KIM	CHECKED HH. TSUKUMO	DATE 20200902
APPROVED : AR. SHIRAI		20180601		DRAWING NO. EDC-169254-10-00			
CHECKED : HS. OZAWA		20180601		PART NO. GT25H2-8DP-2.2H(10)			
DESIGNED : YT. HAYAKAWA		20180601		CODE NO. CL775-0047-4-10			
DRAWN : YT. HAYAKAWA		20180601					

HRS DRAWING FOR REFERENCE

In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Dec.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

PACKAGING SPECIFICATION



△ REEL DIMENSION (FREE)

PRODUCTS DIRECTION

FIXING EMBOSSED CARRIER TAPE

PLASTIC REEL

(37.4 :WIDE OF OUTSIDE)

(Ø 380)

(33.4 :WIDE OF INSIDE)

200 PCS/REEL

φ 1.5 CARRIER HOLES AT FRONT

4 EMPTY POCKETS MIN


6 EMPTY POCKETS MIN

FIXING EMBOSSED CARRIER TAPE

CARDBOARD DIMENSION(FREE)

BOX SIZE

W=(405) (mm)
 D=(405) (mm)
 H=(39) (mm)



1 REEL/BOX

HRS	DRAWING NO.	EDC-169254-10-00	2/2
	PART NO.	GT25H2-8DP-2.2H(10)	
	CODE NO.	CL775-0047-4-10	