

APPLICABLE STANDARD								
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO +105 °C (NOTE1)		STORAGE TEMPERATURE RANGE	-40 °C TO +105 °C			
	VOLTAGE	250 V AC		CURRENT	3 A			
SPECIFICATIONS								
ITEM		TEST METHOD		REQUIREMENTS		QT AT		
CONSTRUCTION								
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		x	x	
MARKING		CONFIRMED VISUALLY.				x	x	
ELECTRIC CHARACTERISTICS								
CONTACT RESISTANCE		1A DC.		30 mΩ MAX.		—	—	
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD		20 mV AC MAX, 0.1 mA(OR 1kHz)		30 mΩ MAX.		—	—	
INSULATION RESISTANCE		500 V DC		100 MΩ MIN.		x	—	
VOLTAGE PROOF		1000 V AC FOR 1 MIN.		NO FLASHOVER OR BREAKDOWN.		x	—	
MECHANICAL CHARACTERISTICS								
CONTACT MATING FORCE		100mm/min WITH CONTACT ITSELF		INSERTION FORCE : 4.9N MAX.		—	—	
MECHANICAL OPERATION		30 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 60 mΩ MAX..		—	—	
				② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.		x	—	
VIBRATION		FREQUENCY 20 TO 400 Hz, 43.1m/s ² , AT 3h FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 10 μs.		—	—	
				② CONTACT RESISTANCE:60 mΩ MAX		—	—	
				③ NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.		x	—	
SHOCK		FREQUENCY 20 TO 50 Hz,66.6m/ s ² AT 1 h.		① NO ELECTRICAL DISCONTINUITY OF 10 μs.		—	—	
				② CONTACT RESISTANCE:60 mΩ MAX		—	—	
				③ NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.		x	—	
LOCK STRENGTH		APPLYING A PULL FORCE THE MATING AXIALLY AT 98N MAX.		① DURING APPLYING,MATING COMPLETELY.		x	—	
				② AFTER APPLYING,NO DEFECT OF MATING PARTS.		x	—	
ENVIRONMENTAL CHARACTERISTICS								
DAMP HEAT (STEADY STATE)		EXPOSED AT 60°C, 90 TO 95%, 500h.		① CONTACT RESISTANCE: 60 mΩ MAX.		—	—	
				② INSULATION RESISTANCE:100 MΩ MIN.		x	—	
				③ NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.		x	—	
RAPID CHANGE OF TEMPERATURE		TEMPERATURE:-40→5 TO 35→120→5 TO 35°C TIME: 30→5→30→5 MIN UNDER 1000 CYCLES.		① CONTACT RESISTANCE: 60 mΩ MAX.		—	—	
				② INSULATION RESISTANCE:100 MΩ MIN.		x	—	
				③ NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.		x	—	
DRY HEAT		EXPOSED AT 105°C, 300h.		① CONTACT RESISTANCE: 60 mΩ MAX.		—	—	
				② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.		x	—	
COLD		EXPOSED AT -40°C, 120h.		① CONTACT RESISTANCE: 60 mΩ MAX.		—	—	
				② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.		x	—	
RESISTANCE TO SO ₂ GAS		EXPOSED IN 500 PPM FOR 8h.		① CONTACT RESISTANCE: 60 mΩ MAX.		—	—	
				② NO HEAVY CORROSION.		x	—	
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED		DATE
△								
REMARK (NOTE1) INCLUDE THE TEMPERATURE RISING BY CURRENT.				APPROVED		AR. SHIRAI		15. 02. 17
				CHECKED		MO. OKADA		15. 02. 17
				DESIGNED		TK. SHISHIKURA		15. 02. 17
				DRAWN		TK. SHISHIKURA		15. 02. 17
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.		ELC-169603-00-00		
HRS	SPECIFICATION SHEET			PART NO.		GT25-24DS-HU		
	HIROSE ELECTRIC CO., LTD.			CODE NO.		CL775-0068-4-00		△ 1/1