


Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

RoHS, ELV COMPLIANT






NOTES
1) RECOMMENDED THICKNESS OF SOLDERING PASTE: 0.15mm
2) RECOMMENDED REFLOW PROFILE (SEE RIGHT GRAPH)
   CYCLE TIME: UP TO 2 CYCLES OF REFLOW SOLDERING ARE POSSIBLE UNDER THE CONDITIONS, PROVIDED THAT THERE IS A RETURN TO NORMAL TEMPERATURE BETWEEN THE FIRST AND SECOND CYCLE.
   PEAK TEMPERATURE: 250℃
   230℃ MIN. FOR 20 TO 40 SECONDS.
   PREHEATING AREA 150-180℃ FOR 60 TO 120 SECONDS.
3) HAND SOLDERING: 280-300℃, 2S MAX.
4) CONTACT COPLANARITY: 0.1mm MAX.
5) RECOMMENDED THICKNESS OF PCB: 1.2-1.6mm
6) FOR THE PREVENTION EXCESSIVE STRESS FOR CONNECTOR AND PCB, WE RECOMMEND ADDITIONAL SUPPORT MECHANISM IF THE FLANGE WAS ELIMINATED.




HRS DRAWING FOR REFERENCE


RECOMMENDE PCB LAYOUT




PANNEL LAYOUT



MATED CONNECTORS



VIEW A (4:1)



NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
2	PPS	BLUE	4	BRASS	TIN PLATING
1	COPPER ALLOY	TIN PLATING	3	BRASS	TIN PLATING


UNITS	SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2 : 1	0				


HIROSE ELECTRIC CO., LTD.


APPROVED	KI. HIROKAWA	20200331
CHECKED	EJ. WAKATSUKI	20200330
DESIGNED	TS. KUBOTA	20200325
DRAWN	YK. MITSUISHI	20200317


DRAWING NO. EDC-167011-58-00
PART NO. GT17HN-4DP-2H(C)(58)
CODE NO. CL767-0176-2-58
0 1/2

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.










HRS DRAWING FOR REFERENCE



PACKAGE STYLE

NOTE 1. 300 PCS / REEL
NOTE 2. TOP COVER TAPE PEEL FORCE TO BE 0.1 TO 0.7 N AFTER SEALING.

DRAWING NO.	EDC-167011-58-00
PART NO.	GT17HN-4DP-2H(C)(58)
CODE NO.	CL767-0176-2-58

△0 2/2