

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO 105 °C (NOTE1)		STORAGE TEMPERATURE RANGE	-40 °C TO 105 °C	
	VOLTAGE	250 V AC		CURRENT	1 A	
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS		QT AT
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		○ ○
MARKING		CONFIRMED VISUALLY.				○ ○
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE		1A DC.		SIGNAL: 30 mΩ MAX, SHIELD: 60 mΩ MAX .		○ -
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD		20 mV AC MAX, 0.1 mA(DC OR 1000Hz)		SIGNAL: 30 mΩ MAX, SHIELD: 60 mΩ MAX .		○ -
INSULATION RESISTANCE		500 V DC		100 MΩ MIN.		○ -
VOLTAGE PROOF		650 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.		○ -
MECHANICAL CHARACTERISTICS						
CONTACT INSERTION AND EXTRACTION FORCES		BY STEEL GAUGE, -.		INSERTION FORCE - N MAX. EXTRACTION FORCE - N MIN.		- -
MECHANICAL OPERATION		30 TIMES INSERTIONS AND EXTRACTIONS.		① SIGNAL:30mΩ MAX, SHIELD:60mΩ MAX . ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		○ -
VIBRATION		FREQUENCY 20 TO 200 Hz, 43.1 m/s ² AT 3 h FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② SIGNAL:30mΩ MAX, SHIELD:60mΩ MAX . ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		○ -
SHOCK		FREQUENCY 20 TO 50 Hz, 66.6 m/s ² AT 1 h .		① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② SIGNAL:30mΩ MAX, SHIELD:60mΩ MAX . ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		○ -
LOCK STRENGTH		APPLYING A PULL FORCE THE MATING AXIALLY AT 78.4N MAX.		① DURING APPLYING,MATING COMPLETELY. ② AFTER APPLYING,NO DEFECT OF MATING PARTS.		○ -
ENVIRONMENTAL CHARACTERISTICS						
DAMP HEAT (STEADY STATE)		EXPOSED AT 60 °C, 90 ~ 95 %, 500 h.		① SIGNAL:60mΩ MAX, SHIELD:120mΩ MAX . ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		○ -
RAPID CHANGE OF TEMPERATURE		TEMPERATURE-40→5 TO 35→ 85→5 TO 35°C TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.		① SIGNAL:60mΩ MAX, SHIELD:120mΩ MAX . ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		○ -
DRY HEAT		EXPOSED AT 105°C, 300 h.		① SIGNAL:60mΩ MAX, SHIELD:120mΩ MAX . ② NO HEAVY CORROSION.		○ -
COLD		EXPOSED AT -55°C , 120 h.		① SIGNAL:60mΩ MAX, SHIELD:120mΩ MAX . ② NO HEAVY CORROSION.		○ -
RESISTANCE TO SOLDERING HEAT		SOLDER TEMPERATURE, 260 °C FOR IMMERSION, DURATION, 10s.		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.		○ -
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 245 °C FOR IMMERSION DURATION, 3s.		A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.		○ -
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
△						
REMARK			APPROVED	KS. SATOH	08. 03. 14	
(NOTE1) INCLUDE THE TEMPERATURE RISING BY CURRENT.			CHECKED	KS. SATOH	08. 03. 14	
(NOTE2) TAPPLICABLE BOARD : 1.6±0.2			DESIGNED	TY. IKEDA	08. 03. 03	
			DRAWN	TY. IKEDA	08. 03. 03	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-167040-00	
HRS	SPECIFICATION SHEET		PART NO.	GT17H-4P-2DSA		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL767-0181-2-00 △ 1/1		