





Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


ELV, RoHS COMPLIANT





MATED CONNECTORS




RECOMMENDED PCB LAYOUT
(3:1)



RECOMMENDED PANEL CUTOUT




350 PCS/REEL



※ Embossed pocket has a different shape to prevent overlapping,
and the drawing shows a representative shape.

NOTES

1. RECOMMENDED REFLOW PROFILE (SEE RIGHT GRAPH)
CYCLE TIME: UP TO 2 CYCLES OF REFLOW SOLDERING ARE POSSIBLE
UNDER THE CONDITIONS, PROVIDED THAT THERE IS
A RETURN TO NOMAL TEMPERATURE BETWEEN THE FIRST
AND SECOND CYCLE.
PEAK TEMPERATURE: 250°C
230°C MIN, FOR 20 TO 40 SECONDS.
PREHEATING AREA 150~180°C FOR 60 TO 120 SECONDS.
2. HAND SOLDERING: 280~300°C, 2SECONDS MAX.
3. CONTACT COPLANARITY: 0.1mm MAX.
4. RECOMMENDED THICKNESS OF PCB: 1.6mm
5. RECOMMENDED THICKNESS OF SOLDERING PASTE: 0.12mm



2	PA	DARK GRAY	4	BRASS	TIN PLATING
1	COPPER ALLOY	TIN PLATING	3	BRASS	TIN PLATING
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 2:1	COUNT 0	DESCRIPTION OF REVISIONS DIS-T-00018457	DESIGNED KN. YANAGIMOTO
		APPROVED : AR. SHIRAI	2019. 01. 11	DRAWING NO.	EDC-353182-12-01
		CHECKED : TH. MIZUGUCHI	2019. 01. 10	PART NO.	GT32-4DP-1.5H(12)
		DESIGNED : TS. KUBOTA	2019. 01. 10	CODE NO.	CL0782-0038-1-12
		DRAWN : TS. KUBOTA	2019. 01. 10		
					DATE 2023. 06. 27