

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO 105 °C (NOTE1)		STORAGE TEMPERATURE RANGE	-40 °C TO 105 °C	
	VOLTAGE	50 V DC		CURRENT	1 A	
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS		QT AT
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		x x
MARKING		CONFIRMED VISUALLY.				x x
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE		1A DC.		50 mΩ MAX.		x -
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD		20 mV AC MAX, 0.1 mA(DC OR 1000Hz)		50 mΩ MAX.		x -
INSULATION RESISTANCE		500 V DC		100 MΩ MIN.		x -
VOLTAGE PROOF		125 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.		x -
MECHANICAL CHARACTERISTICS						
MECHANICAL OPERATION		30 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 150 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x -
VIBRATION		FREQUENCY 20 TO 200 Hz, 43.1 m/s ² AT 3 h FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② CONTACT RESISTANCE: 150 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x -
SHOCK		FREQUENCY 20 TO 50 Hz, 66.6 m/s ² AT 1 h.		① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② CONTACT RESISTANCE: 150 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x -
LOCK STRENGTH		APPLYING A PULL FORCE THE MATING AXIALLY AT 98N MAX.		① DURING APPLYING,MATING COMPLETELY. ② AFTER APPLYING,NO DEFECT OF MATING PARTS.		- -
ENVIRONMENTAL CHARACTERISTICS						
DAMP HEAT (STEADY STATE)		EXPOSED AT 60 °C, 90 ~ 95 %, 500 h.		① CONTACT RESISTANCE: 150 mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x -
RAPID CHANGE OF TEMPERATURE		TEMPERATURE-40→5 TO 35→85→5 TO 35°C TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.		① CONTACT RESISTANCE: 150 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x -
DRY HEAT		EXPOSED AT 105°C, 300 h.		① CONTACT RESISTANCE: 150 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x -
COLD		EXPOSED AT -40°C , 120 h.		① CONTACT RESISTANCE: 150 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x -
RESISTANCE TO SO ₂ GAS		EXPOSED IN 25 PPM FOR 96h.		① CONTACT RESISTANCE: 150 mΩ MAX. ② NO HARMFUL CORROSION.		x -
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
△						
REMARK				APPROVED	NH. NAKATA	14. 06. 09
(NOTE1) INCLUDE THE TEMPERATURE RISING BY CURRENT.				CHECKED	KI. HIROKAWA	14. 06. 09
(NOTE2) CONTACT RESISTANCE OF INNER CONDUCTOR AFTER ENVIRONMENTAL AND DURABILITY TEST SHALL BE 100mΩ.				DESIGNED	HS. NAGANO	14. 06. 09
				DRAWN	HS. NAGANO	14. 06. 09
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.		ELC4-168975-00
HRS	SPECIFICATION SHEET		PART NO.	GT36-1. 6-2. 9SCF (A)		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL786-0004-5-00 △ 1/1		