







Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

ELV, RoHS COMPLIANT




- NOTE1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW (REFER TO RIGHT FIG.)  
USED REFLOW SYSTEM : IR IN THE AIR OR NITROGEN  
NO. OF CYCLES : 2 MAX  
PEAK : 250°C  
OVER 230°C : 20~40s  
PREHEAT : 150~180°C 60~120s  
2. TEMPERATURE FOR SOLDERING IRON : 280~300°C WITHIN 2s  
3. COPLANARITY SHALL BE 0.1mm MAX.  
4. RECOMMENDED PCB THICKNESS IS 1.6mm  
5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.



3	BRASS	TIN PLATED	6	PET	
2	BRASS	TIN PLATED	5	PS	
1	PA	BLACK	4	BRASS	TIN PLATED
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS	mm	SCALE	2 : 1	COUNT	1
DESCRIPTION OF REVISIONS			DESIGNED	CHECKED	DATE
DIS-T-00006626			DONGCHAN KIM	HH. TSUKUMO	20200902
APPROVED : AR. SHIRAI 20180601			DRAWING NO. EDC-169254-10-00		
CHECKED : HS. OZAWA 20180601			PART NO. GT25H2-8DP-2.2H(10)		
DESIGNED : YT. HAYAKAWA 20180601			CODE NO. CL775-0047-4-10		
DRAWN : YT. HAYAKAWA 20180601			1/2		

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

# PACKAGING SPECIFICATION



HRS DRAWING FOR REFERENCE

<b>HRS</b>	DRAWING NO.	EDC-169254-10-00	2/2
	PART NO.	GT25H2-8DP-2.2H<10>	
	CODE NO.	CL775-0047-4-10	