






Jan.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

ELV. RoHS COMPLIANT




PIN ASSIGNMENT
10 20 9 19 8 18 7 17 6 16 5 15 4 14 3 13 2 12 1 11




HRS DRAWING FOR REFERENCE

- NOTE1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW (REFER TO RIGHT FIG.) USED REFLOW SYSTEM
 : IR IN THE AIR OR NITROGEN
 NO. OF CYCLES : 2 MAX
 PEAK : 250°C
 OVER 230°C : 20~40s
 PREHEAT : 150~180°C
 60~120s
2. TEMPERATURE FOR SOLDERING IRON : 280~300°C WITHIN 2s
3. LEAD CO-PLANARITY SHALL BE 0.1mm MAX.
4. RECOMMENDED PCB THICKNESS IS 1.6mm
5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.



3	BRASS	TIN PLATED	6	PET			
2	BRASS	TIN PLATED	5	PS			
1	PA	BLACK	4	BRASS	TIN PLATED		
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS		
UNITS mm		SCALE 2 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-T-00006626	DESIGNED DONGCHAN KIM	CHECKED HH. TSUKUMO	DATE 20200902
HRS HIROSE ELECTRIC CO., LTD.		APPROVED : AR. SHIRAI	20180622	DRAWING NO. EDC-358751-10-00		PART NO. GT25H2-20DP-2. 2H<10>	
		CHECKED : HS. OZAWA	20180622	CODE NO. CL775-0080-0-10		1/2	
		DESIGNED : YT. HAYAKAWA	20180622				
		DRAWN : GYEONGMIN LEE	20180622				

Jan.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



HRS	DRAWING NO.	EDC-358751-10-00
	PART NO.	GT25H2-20DP-2.2H<10>
	CODE NO.	CL775-0080-0-10

2/2