








ELV, RoHS COMPLIANT



- NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW (REFER TO RIGHT FIG.)
 USED REFLOW SYSTEM
 : IR IN THE AIR OR NITROGEN
 NO. OF CYCLES : 2 MAX
 PEAK : 250°C
 OVER 230°C : 20~40s
 PREHEAT : 150~180°C
 : 60~120s
 2. TEMPERATURE FOR SOLDERING IRON : 280~300°C WITHIN 2s
 3. CO-PLANARITY SHALL BE 0.1mm MAX.
 4. RECOMMENDED PCB THICKNESS IS 1.6mm.
 5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.



| | | | | | |
|---------------------------|----------|-------------------|-------|------------------------------|--------------------------|
| 2 | BRASS | TIN PLATED T=0.64 | 4 | BRASS | TIN PLATED T=0.4 |
| 1 | PPS | BLACK | 3 | BRASS | TIN PLATED T=0.64 |
| NO. | MATERIAL | FINISH . REMARKS | NO. | MATERIAL | FINISH . REMARKS |
| UNITS | mm | SCALE | 2 : 1 | COUNT | DESCRIPTION OF REVISIONS |
| APPROVED : AR. SHIRAI | | 16.07.27 | | DRAWING NO. EDC-360215-00-00 | |
| CHECKED : HS. OZAWA | | 16.07.27 | | PART NO. GT25H2-40DP-2.2V | |
| DESIGNED : TK. SHISHIKURA | | 16.07.27 | | CODE NO. CL775-0085-3-00 | |
| DRAWN : TK. SHISHIKURA | | 16.07.27 | | 1/1 | |

Jan.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved. In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.