








Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

ELV, RoHS COMPLIANT



- NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW (REFER TO RIGHT FIG.)
USED REFLOW SYSTEM : IR IN THE AIR OR NITROGEN
NO. OF CYCLES : 2 MAX
PEAK : 250°C
OVER 230°C : 20~40s
PREHEAT : 150~180°C
60~120s
2. TEMPERATURE FOR SOLDERING IRON : 280~300°C WITHIN 2s
3. CO-PLANARITY SHALL BE 0.1mm MAX.
4. RECOMMENDED PCB THICKNESS IS 1.6mm.
5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.



| 2 | BRASS | TIN PLATED T=0.64 | 4 | BRASS | TIN PLATED T=0.4 | | |
|---------------------------|----------|-------------------|-------|--------------------------|------------------------------|---------|------|
| 1 | PPS | BLACK | 3 | BRASS | TIN PLATED T=0.64 | | |
| NO. | MATERIAL | FINISH . REMARKS | NO. | MATERIAL | FINISH . REMARKS | | |
| UNITS | ⊙ | SCALE | COUNT | DESCRIPTION OF REVISIONS | DESIGNED | CHECKED | DATE |
| mm | | 2 : 1 | △ | | | | |
| APPROVED : AR. SHIRAI | | | | 16.07.27 | DRAWING NO. EDC-360215-00-00 | | |
| CHECKED : HS. OZAWA | | | | 16.07.27 | PART NO. GT25H2-40DP-2.2V | | |
| DESIGNED : TK. SHISHIKURA | | | | 16.07.27 | CODE NO. CL775-0085-3-00 | | |
| DRAWN : TK. SHISHIKURA | | | | 16.07.27 | 1/1 | | |