







1	2	3	4																														
A				A																													
B	<table border="1" data-bbox="1037 582 1348 750"><thead><tr><th>Part No.</th><th>Cable color</th></tr></thead><tbody><tr><td>~068*1~</td><td>GRAY</td></tr><tr><td>~068*2~</td><td>BLACK</td></tr><tr><td>~068*3~</td><td>WHITE</td></tr></tbody></table>			Part No.	Cable color	~068*1~	GRAY	~068*2~	BLACK	~068*3~	WHITE	B																					
Part No.	Cable color																																
~068*1~	GRAY																																
~068*2~	BLACK																																
~068*3~	WHITE																																
C	<p>NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.</p> <p>2 Tolerance for [L]</p> <table border="1" data-bbox="454 1041 1061 1243"><thead><tr><th>Length L [mm]</th><th>Tolerance [mm]</th></tr></thead><tbody><tr><td>100 ≦ L ≦ 200</td><td>±4</td></tr><tr><td>200 < L ≦ 500</td><td>±8</td></tr><tr><td>500 < L ≦ 1000</td><td>±12</td></tr><tr><td>1000 < L</td><td>±1.5%</td></tr></tbody></table>			Length L [mm]	Tolerance [mm]	100 ≦ L ≦ 200	±4	200 < L ≦ 500	±8	500 < L ≦ 1000	±12	1000 < L	±1.5%	C																			
Length L [mm]	Tolerance [mm]																																
100 ≦ L ≦ 200	±4																																
200 < L ≦ 500	±8																																
500 < L ≦ 1000	±12																																
1000 < L	±1.5%																																
D	<p>3 Connector rotation angle is within ±45 degree from the above image. For long length in the case of L>500, the angle is optional.</p> <p>4. Specifications are subject to change without notice.</p> <p>【 DIMENSIONS OF CONNECTOR 】</p> 			D																													
E	<table border="1" data-bbox="183 1870 1141 1948"><tbody><tr><td>1</td><td>X.FL-LP(P)-068</td><td>CL331-0714-0</td><td>2</td><td>1.13 Dia. coaxial cable</td></tr><tr><td>NO.</td><td>PART NO.</td><td>CODE NO.</td><td>NO.</td><td>PART NO.</td></tr></tbody></table> <div data-bbox="1308 1870 1476 1915">HALOGEN FREE</div>			1	X.FL-LP(P)-068	CL331-0714-0	2	1.13 Dia. coaxial cable	NO.	PART NO.	CODE NO.	NO.	PART NO.	E																			
1	X.FL-LP(P)-068	CL331-0714-0	2	1.13 Dia. coaxial cable																													
NO.	PART NO.	CODE NO.	NO.	PART NO.																													
F	<table border="1" data-bbox="183 1960 1508 2161"><thead><tr><th>UNITS mm</th><th>SCALE FREE</th><th>COUNT</th><th>DESCRIPTION OF REVISIONS</th><th>DESIGNED</th><th>CHECKED</th><th>DATE</th></tr></thead><tbody><tr><td rowspan="4"></td><td rowspan="4">HIROSE ELECTRIC CO., LTD.</td><td>APPROVED</td><td>・NK. NINOMIYA</td><td>20200313</td><td colspan="2">DRAWING NO.</td></tr><tr><td>CHECKED</td><td>・MT. KANEKO</td><td>20200312</td><td colspan="2">PART NO.</td></tr><tr><td>DESIGNED</td><td>・MK. INOUE</td><td>20200312</td><td colspan="2">CODE NO.</td></tr><tr><td>DRAWN</td><td>・MK. INOUE</td><td>20200312</td><td colspan="2">X. FL-2LPP-068**T-A-L</td></tr></tbody></table> <div data-bbox="1412 2116 1508 2161"> 1/1</div>			UNITS mm	SCALE FREE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE		HIROSE ELECTRIC CO., LTD.	APPROVED	・NK. NINOMIYA	20200313	DRAWING NO.		CHECKED	・MT. KANEKO	20200312	PART NO.		DESIGNED	・MK. INOUE	20200312	CODE NO.		DRAWN	・MK. INOUE	20200312	X. FL-2LPP-068**T-A-L		F
UNITS mm	SCALE FREE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE																											
	HIROSE ELECTRIC CO., LTD.	APPROVED	・NK. NINOMIYA	20200313	DRAWING NO.																												
		CHECKED	・MT. KANEKO	20200312	PART NO.																												
		DESIGNED	・MK. INOUE	20200312	CODE NO.																												
		DRAWN	・MK. INOUE	20200312	X. FL-2LPP-068**T-A-L																												