

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO 105 °C (NOTE1)		STORAGE TEMPERATURE RANGE	-40 °C TO 105 °C	
	VOLTAGE	30 V AC		CURRENT	1 A	
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS		QT AT
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		x x
MARKING		CONFIRMED VISUALLY.				x x
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE		1A DC.		SIGNAL : 30 mΩ MAX, SHIELD : 60 mΩ MAX .		x -
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD		20 mV AC MAX, 0.1 mA(DC OR 1000Hz)		SIGNAL : 30 mΩ MAX, SHIELD : 60 mΩ MAX .		x -
INSULATION RESISTANCE		500 V DC		100 MΩ MIN.		x -
VOLTAGE PROOF		500 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.		x -
MECHANICAL CHARACTERISTICS						
CONTACT INSERTION AND EXTRACTION FORCES		— BY STEEL GAUGE.		INSERTION FORCE — N MAX. EXTRACTION FORCE — N .		- -
MECHANICAL OPERATION		30 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE : SIGNAL : 60 mΩ MAX, SHIELD : 120 mΩ MAX . ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x - x -
VIBRATION		FREQUENCY 20 TO 200 Hz, 43.1 m/s ² AT 3 h FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② CONTACT RESISTANCE : SIGNAL : 60 mΩ MAX, SHIELD : 120 mΩ MAX . ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x - x - x -
SHOCK		ACCELERATION 981m/s ² ,6ms AT 3 TIMES FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② CONTACT RESISTANCE : SIGNAL : 60 mΩ MAX, SHIELD : 120 mΩ MAX . ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x - x - x -
LOCK STRENGTH		APPLYING A PULL FORCE THE MATING AXIALLY AT 98N MAX.		① DURING APPLYING,MATING COMPLETELY. ② AFTER APPLYING,NO DEFECT OF MATING PARTS.		x - x -
ENVIRONMENTAL CHARACTERISTICS						
DAMP HEAT (STEADY STATE)		EXPOSED AT 60 °C, 90 ~ 95 %, 500 h.		① CONTACT RESISTANCE : SIGNAL : 60 mΩ MAX, SHIELD : 120 mΩ MAX . ② INSULATION RESISTANCE : 100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x - x - x -
RAPID CHANGE OF TEMPERATURE		TEMPERATURE-40→5 TO 35→ 85→5 TO 35°C TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.		① CONTACT RESISTANCE : SIGNAL : 60 mΩ MAX, SHIELD : 120 mΩ MAX . ② INSULATION RESISTANCE : 100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x - x - x -
DRY HEAT		EXPOSED AT 105°C, 1000 h.		① CONTACT RESISTANCE : SIGNAL : 60 mΩ MAX, SHIELD : 120 mΩ MAX . ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x - x -
COLD		EXPOSED AT -40°C, 1000 h.		① CONTACT RESISTANCE : SIGNAL : 60 mΩ MAX, SHIELD : 120 mΩ MAX . ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		x - x -
RESISTANCE TO SO ₂ GAS		EXPOSED IN 500 PPM FOR 8 h.		① CONTACT RESISTANCE : SIGNAL : 60 mΩ MAX, SHIELD : 120 mΩ MAX .		x -
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED
REMARK				APPROVED		NH. NAKATA
(NOTE1) INCLUDE THE TEMPERATURE RISING BY CURRENT.				CHECKED		TS. KUBOTA
				DESIGNED		MH. SHOUJI
				DRAWN		MH. SHOUJI
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.		ELC4-169594-00
HRS		SPECIFICATION SHEET		PART NO.		GT32-19DP-0. 75CB
		HIROSE ELECTRIC CO., LTD.		CODE NO.		CL782-0032-5-00
						△ 1/1