







Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



RECOMMENDED LAND PATTERN DIMENSION OF PCB



③ PCB DISTANCE






② FX26-40P-1SV
(Mating connector)

FX26-40S-1SV20

20 ± 0.75

- Note
- Lead CO-Planarity is 0.1mm MAX.
 - Floating range of the mating connector is ±0.7mm MAX.
The maximum cycle time of the floating operation is in accordance with the mating cycle of the connector.
 - Please use the connectors within the specified PCB distance.
 - Blemish and hit mark can be occurred through out the manufacturing process which doesn't affect quality level.
 - The dimensions in parentheses are for references.
 - This is packaged in embossed carrier tape. (200pcs/RL)
 - It shows the vacuum pickup area.
Remove the pickup cap before mating connectors.
 - This connector has no polarity with the mating connector.

6	POLYAMIDE	(CAP FOR VACUUM PICKUP)
5	POLYESTER	(EMBOSSED COVER TAPE)
4	POLYSTYRENE	(EMBOSSED CARRIER TAPE)
3	PHOSPHOR BRONZE	OVER PLATING : TIN-PLATING 1μm UNDER PLATING: NICKEL 0.5μm
2	COPPER ALLOY	CONTACT AREA : GOLD 0.1μm LEAD AREA : GOLD 0.03μm UNDER PLATING: NICKEL 1μm

1	POLYAMIDE		BLACK UL94V-0		NO.		MATERIAL		FINISH . REMARKS		
NO.		MATERIAL		FINISH . REMARKS		NO.		MATERIAL		FINISH . REMARKS	
UNITS mm				SCALE 2 : 1		COUNT 2	DESCRIPTION OF REVISIONS DIS-F-00006551		DESIGNED KI. YAMAZAKI	CHECKED KN. SHIBUYA	DATE 20200831
 HIROSE ELECTRIC CO., LTD.		APPROVED : HH. SHINDO		20200402		DRAWING NO. EDC-376650-00-00					
		CHECKED : KN. SHIBUYA		20200402		PART NO. FX26-40S-1SV20					
		DESIGNED : KI. YAMAZAKI		20200402		CODE NO. CL576-1304-0-00					
		DRAWN : KI. YAMAZAKI		20200402							
											

8