

APPLICABLE STANDARD						
Operating condition	Operating temperature range	-30 to +85 [degree C] (20 to 80%RH)	Storage temperature range	-10 to +60 [degree C] (40 to 70%RH)		
	Characteristic impedance		Applicable cable			
	Applicable Connector					
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION						
Dimension, Constraction and Finishing		Shall be carried out visually and measuring instrument.		According to drawing	X	X
Marking		Confirmed visually			X	X