



Jan.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




- NOTE 1 All lead co-planarity shall be 0.1mm maximum.
- ①② Contact plating
 - Contact area :Gold 0.05um MIN
 - SMT lead :Gold 0.05um MIN
 - Under plating:Nickel 1um MIN
 - ①③ Shell plating
 - All area :Gold 0.05um MIN
 - Under plating:Nickel 1um MIN 2um MAX
 - ④ The peeling strength of cover tape shall comply with IEC 60286-3 (JIS C0806-3).
 - ⑤ Embossed carrier tape has the sprocket hole on one side.
 - ⑥ Recommended land pattern is shown. Please do not arrange the via without resist in the hatching part as shown in the figure.
 - ⑦ The connector dimension when the plug engages is shown.
 - ⑧ Please note that it becomes impossible to use extraction tool when other parts are in the crossing hatching part as shown in the figure.
 - ⑨ Please pay attention to the PCB pattern and fiber alignment, considering not to overload fiber. (Please see ETAD-K0398 about connector handling precautions.)
 - ⑩ Pin assignment and functions are described in the specification of BF4M plug connector (ETAD-K0485)




3	Phosphor Bronze	③	5	POLYESTER	CLEAR (Cover tape)
2	Phosphor Bronze	②	4	PS	CLEAR (Embossed carrier tape)
1	LCP	UL94 V-0			
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 10 : 1	COUNT 4	DESCRIPTION OF REVISIONS DIS-K-002978	DESIGNED SJ. SUZUKI
HIROSE ELECTRIC CO., LTD.		APPROVED : MT. SHIBUTANI 13.03.01	DESIGNED	CHECKED	DATE
		CHECKED : SJ. SHIMIZU 13.03.01	DRAWING NO. EDC3-178304-10		
		DESIGNED : KS. JOKURA 13.02.28	PART NO. BF4-RX-14DS-0.5V<10>		
		DRAWN : KS. JOKURA 13.02.28	CODE NO. CL831-0009-9-10		
			①②		

Jan.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


Dimensions of embossed carrier tape (Scale : FREE)




Packing style (Scale : FREE)




Recommended reflow temperature profile using Lead-Free solder paste.



Recommended PCB land pattern




Recommended metal mask dimensions (Mask thickness : 120 μm)



Aperture ratio
 Pads mounted contacts : 70%
 Pads mounted shell : 100%

Dimensions of engaged connector (Scale:FREE)



HRS	DRAWING NO.	EDC3-178304-10
	PART NO.	BF4-RX-14DS-0.5V<10>
	CODE NO.	CL831-0009-9-10
		2/2