



1	2	3	4																																							
A				A																																						
B	<table border="1" data-bbox="1037 627 1348 761"><thead><tr><th>Part No.</th><th>Cable color</th></tr></thead><tbody><tr><td>~04*1TV~</td><td>WHITE</td></tr><tr><td>~04*2TV~</td><td>BLACK</td></tr></tbody></table>			Part No.	Cable color	~04*1TV~	WHITE	~04*2TV~	BLACK	B																																
Part No.	Cable color																																									
~04*1TV~	WHITE																																									
~04*2TV~	BLACK																																									
C	<p>NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.</p> <p>2 Tolerance for [L]</p> <table border="1" data-bbox="454 1041 1061 1243"><thead><tr><th>Length L [mm]</th><th>Tolerance [mm]</th></tr></thead><tbody><tr><td>35 ≤ L ≤ 200</td><td>±4</td></tr><tr><td>200 < L ≤ 500</td><td>±8</td></tr><tr><td>500 < L ≤ 1000</td><td>±12</td></tr><tr><td>1000 < L</td><td>±1.5%</td></tr></tbody></table>			Length L [mm]	Tolerance [mm]	35 ≤ L ≤ 200	±4	200 < L ≤ 500	±8	500 < L ≤ 1000	±12	1000 < L	±1.5%	C																												
Length L [mm]	Tolerance [mm]																																									
35 ≤ L ≤ 200	±4																																									
200 < L ≤ 500	±8																																									
500 < L ≤ 1000	±12																																									
1000 < L	±1.5%																																									
D	<p>3 Connector rotation angle is within ±45 degree from the above image. For long length in the case of L>500, the angle is optional.</p> <p>4. Specifications are subject to change without notice.</p> <p>【 DIMENSIONS OF CONNECTOR 】</p> 			D																																						
E	<table border="1" data-bbox="183 1870 1508 1948"><tr><td>1</td><td>U.FL-LP-040HF</td><td>CL331-0557-3</td><td>2</td><td>0.81 Dia. coaxial cable</td><td rowspan="2">HALOGEN FREE</td></tr><tr><td>NO.</td><td>PART NO.</td><td>CODE NO.</td><td>NO.</td><td>PART NO.</td></tr></table>			1	U.FL-LP-040HF	CL331-0557-3	2	0.81 Dia. coaxial cable	HALOGEN FREE	NO.	PART NO.	CODE NO.	NO.	PART NO.	E																											
1	U.FL-LP-040HF	CL331-0557-3	2	0.81 Dia. coaxial cable	HALOGEN FREE																																					
NO.	PART NO.	CODE NO.	NO.	PART NO.																																						
F	<table border="1" data-bbox="183 1948 1508 2161"><tr><td>UNITS mm</td><td></td><td>SCALE FREE</td><td>COUNT </td><td>DESCRIPTION OF REVISIONS</td><td>DESIGNED</td><td>CHECKED</td><td>DATE</td></tr><tr><td colspan="2"></td><td colspan="2">APPROVED : NK. NINOMIYA 20201028</td><td colspan="4">DRAWING NO.</td></tr><tr><td colspan="2" rowspan="3">HIROSE ELECTRIC CO., LTD.</td><td colspan="2">CHECKED : MT. KANEKO 20201027</td><td colspan="4">PART NO. UFL-2LPHF6-04**TV-AE-L 1</td></tr><tr><td colspan="2">DESIGNED : MS. MATSUMOTO 20201027</td><td colspan="4">CODE NO.</td></tr><tr><td colspan="2">DRAWN : MS. MATSUMOTO 20201027</td><td colspan="4"></td></tr></table>					UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE			APPROVED : NK. NINOMIYA 20201028		DRAWING NO.				HIROSE ELECTRIC CO., LTD.		CHECKED : MT. KANEKO 20201027		PART NO. UFL-2LPHF6-04**TV-AE-L 1				DESIGNED : MS. MATSUMOTO 20201027		CODE NO.				DRAWN : MS. MATSUMOTO 20201027						F
UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE																																			
		APPROVED : NK. NINOMIYA 20201028		DRAWING NO.																																						
HIROSE ELECTRIC CO., LTD.		CHECKED : MT. KANEKO 20201027		PART NO. UFL-2LPHF6-04**TV-AE-L 1																																						
		DESIGNED : MS. MATSUMOTO 20201027		CODE NO.																																						
		DRAWN : MS. MATSUMOTO 20201027																																								
FORM HC0011-5-51						2 3 4																																				