

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	① -25 °C TO 60 °C	STORAGE TEMPERATURE RANGE	-25 °C TO 60 °C		
	VOLTAGE	—	OPERATING HUMIDITY RANGE	95 % MAX		
	CURRENT	—	APPLICABLE CABLE	—		
SPECIFICATIONS						
ITEM		TEST METHOD	REQUIREMENTS		QT	AT
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.		X	X
MARKING		CONFIRMED VISUALLY.			X	X
① THE OPERATION TEMPERATURE INCLUDES THE TEMPERATURE RISE BY CURRENT CARRYING. ② TEMPERATURE RANGE FOR A CONNECTOR UNMATED.						
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
⚠	1	DIS-E-00002716	TS. ITO	TU. TANIGUCHI	20191127	
REMARK			APPROVED	RI. TAKAYASU	20100617	
			CHECKED	YH. ENAMI	20100617	
			DESIGNED	MT. ITANO	20100617	
			DRAWN	MT. ITANO	20100617	
Unless otherwise specified, refer to IEC 60512. ⚠						
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-025515-61-01	
HRS	SPECIFICATION SHEET		PART NO.		TM11P-88P (61)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.		CL222-1328-2-61	⚠ 1/1