






1	2	3	4																																											
A				A																																										
B	<table border="1" data-bbox="1037 627 1348 761"><thead><tr><th>Part No.</th><th>Cable color</th></tr></thead><tbody><tr><td>~04*1TV~</td><td>WHITE</td></tr><tr><td>~04*2TV~</td><td>BLACK</td></tr></tbody></table>			Part No.	Cable color	~04*1TV~	WHITE	~04*2TV~	BLACK	B																																				
Part No.	Cable color																																													
~04*1TV~	WHITE																																													
~04*2TV~	BLACK																																													
C	NOTE 1 We indicate the length of the harness on the last of product name, 'L' part. 2 Tolerance for [L] <table border="1" data-bbox="454 1041 1061 1243"><thead><tr><th>Length L [mm]</th><th>Tolerance [mm]</th></tr></thead><tbody><tr><td>35 ≤ L ≤ 200</td><td>±4</td></tr><tr><td>200 < L ≤ 500</td><td>±8</td></tr><tr><td>500 < L ≤ 1000</td><td>±12</td></tr><tr><td>1000 < L</td><td>±1.5%</td></tr></tbody></table>			Length L [mm]	Tolerance [mm]	35 ≤ L ≤ 200	±4	200 < L ≤ 500	±8	500 < L ≤ 1000	±12	1000 < L	±1.5%	C																																
Length L [mm]	Tolerance [mm]																																													
35 ≤ L ≤ 200	±4																																													
200 < L ≤ 500	±8																																													
500 < L ≤ 1000	±12																																													
1000 < L	±1.5%																																													
D	3 Connector rotation angle is within ±45 degree from the above image. For long length in the case of L>500, the angle is optional. 4. Specifications are subject to change without notice.			D																																										
E	【 DIMENSIONS OF CONNECTOR 】 			E																																										
F	<table border="1" data-bbox="183 1870 1508 2161"><thead><tr><th>1</th><th>U.FL-LP-040HF</th><th>CL331-0557-3</th><th>2</th><th>0.81 Dia. coaxial cable</th><th>HALOGEN FREE</th></tr><tr><th>NO.</th><th>PART NO.</th><th>CODE NO.</th><th>NO.</th><th>PART NO.</th><th></th></tr></thead><tbody><tr><td>UNITS mm</td><td></td><td>SCALE FREE</td><td>COUNT </td><td>DESCRIPTION OF REVISIONS</td><td>DESIGNED</td></tr><tr><td colspan="2">APPROVED : NK. NINOMIYA 20201028</td><td colspan="4">DRAWING NO.</td></tr><tr><td colspan="2">CHECKED : MT. KANEKO 20201027</td><td colspan="4">PART NO. UFL-2LPHF6-04**TV-AE-L 1</td></tr><tr><td colspan="2">DESIGNED : MS. MATSUMOTO 20201027</td><td colspan="4">CODE NO.</td></tr><tr><td colspan="2">DRAWN : MS. MATSUMOTO 20201027</td><td colspan="4"> 1/1</td></tr></tbody></table>			1	U.FL-LP-040HF	CL331-0557-3	2	0.81 Dia. coaxial cable	HALOGEN FREE	NO.	PART NO.	CODE NO.	NO.	PART NO.		UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	APPROVED : NK. NINOMIYA 20201028		DRAWING NO.				CHECKED : MT. KANEKO 20201027		PART NO. UFL-2LPHF6-04**TV-AE-L 1				DESIGNED : MS. MATSUMOTO 20201027		CODE NO.				DRAWN : MS. MATSUMOTO 20201027		 1/1				F
1	U.FL-LP-040HF	CL331-0557-3	2	0.81 Dia. coaxial cable	HALOGEN FREE																																									
NO.	PART NO.	CODE NO.	NO.	PART NO.																																										
UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED																																									
APPROVED : NK. NINOMIYA 20201028		DRAWING NO.																																												
CHECKED : MT. KANEKO 20201027		PART NO. UFL-2LPHF6-04**TV-AE-L 1																																												
DESIGNED : MS. MATSUMOTO 20201027		CODE NO.																																												
DRAWN : MS. MATSUMOTO 20201027		 1/1																																												