


May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES ① HAND CRIMPING TOOL. REF. NO. ⑧:
HR10A-TC-02 (CL150-0041-2)
THE HOLE DIAMETER FOR CRIMPING: Ø5.3
- ② THE RECOMMENDED CLAMP TORQUE,
REF. NO. ⑥: 1.5 TO 2 N·m.
- ③ ACROSS FLATS HEXAGON HEAD OF REF. NO. ⑦: 1.27
THE RECOMMENDED CLAMP TORQUE,
REF. NO. ⑦: 0.3 TO 0.4 N·m.
- ④ LOCTITE 263, HENKEL JAPAN OR EQUIVALENT APPLIES
TO PREVENT REF. NO. ① AND ⑦ FROM LOOSENING.
- ⑤ ONE EXAMPLE OF THE ROTATION OF REF. NO. ⑥ TO
REF. NO. ① IS SHOWN.
GOLD PLATING 0.2µm min.
- ⑥ NICKEL UNDER PLATING 2µm min.
- ⑦ THE ASSEMBLY THIS PRODUCT APPLIES TO
THE MANUAL ETAD-C0354-00.

5	STEEL	NICKEL PLATING			
4	BRASS	MATTE FINISH NICKEL PLATED	9	CR	(BLACK)
3	BRASS	⑥	8	BRASS	
2	POLYAMIDE	(BLACK) UL94V-0	7	STEEL	NICKEL PLATING HEXAGON SOCKET SET SCREW M2.6X0.45X2
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	6	BRASS	NICKEL PLATING
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT ② 2	DESCRIPTION OF REVISIONS DIS-C-00016958	DESIGNED HT. ZENBA
HIROSE ELECTRIC CO., LTD.		APPROVED : MO. SATOH	20051223	DRAWING NO.	EDC4-020536-74
		CHECKED : EJ. KUNII	20051222	PART NO.	HR10A-7P-6P(74)
		DESIGNED : DS. MATSUNE	20051221	CODE NO.	CL0110-0303-8-74
		DRAWN : TP. KOMATSU	20051221		② 1/1