







Sep. 1. 2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD 		TÜV approved(R50270424), UL approved(E52653)			
Rating	Operating temperature range ⁽²⁾	-40°C to +105°C	Storage temperature range	-10°C to +60°C	
	Voltage 	AC, DC 600 V(UL,TÜV) AC, DC 1000V	—	—	
	Current ⁽¹⁾ 	10A (UL, TÜV) 20A(When current is applied to all 4pos. except GND)	Applicable cable	φ 11±0.3	
SPECIFICATIONS					
ITEM	TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION					
General Examination	Examined visually and with a measuring instrument.		According to the drawing.	X	X
Marking	Confirmed visually.			X	X
ELECTRICAL CHARACTERISTICS					
Contact Resistance	Measured at DC 1A. MAX.		Center contact 2 mΩ MAX.	X	X
Insulation Resistance	Measured at 500 V DC.		5000 MΩ MIN.	X	X
Voltage Proof	2200 V AC applied for 1 min.		No flashover or breakdown.	X	X
Impulse voltage proof	Apply 15kV standard waveform (1.2/50μs voltage waveform. positive/negative polarities,3 times each) between each contact in mated condition.		No flashover or breakdown.	X	—
MECHANICAL CHARACTERISTICS					
Contact Insertion and Extraction Forces 	Measured with a φ 3.58±0.003 steel gauge.		Insertion and extraction force 0.3 N MIN.	X	—
Mating and Unmating Forces	Measured with an applicable connector.		Mating and unmating force 100 N MAX.	X	—
Contact retention force	Apply pull force to the wire after crimping connected contact.		Do not move the terminal : 50N MAX.	X	—
Mechanical Operation	Mated and unmated 200 times.		Contact resistance: 4 mΩ MAX.	X	—
Vibration	Frequency: 10 → 500 → 10 Hz, Single Amplitude 0.75 mm, Acceleration: 98 m/s ² , 11min/cycle, for 3 h in each of three mutually perpendicular directions.		1) No electrical discontinuity of more than10μs. 2) No damage, cracks or looseness of parts.	X	—
Shock	Acceleration: 490m/s ² , half sine wave pulses of 11ms. Performed 3 times in each of three mutually perpendicular directions.		1) No electrical discontinuity of more than10μs. 2) No damage, cracks or looseness of parts.	X	—
ENVIRONMENTAL CHARACTERISTICS					
Rapid change of temperature	Temperature -55 → R/T ⁽³⁾ → +125 → R/T °C Time 30 → 2 to 3 → 30 → 2 to 3 min under 5 cycles.		1) insulation resistance: 5000 MΩ MIN. 2) No damage, crack and looseness of parts.	X	—
Damp heat (Steady state)	Subjected to 40° C, at a humidity of 90 to 95% for 96h.		1) Insulation resistance: 50 MΩ MIN (At high humidity). 2) Insulation resistance: 500 MΩ MIN (At dry). 3) No damage, crack and looseness of parts.	X	—
Corrosion salt mist ⁽⁴⁾	Subjected to 5% salt spray for 1000h.		No heavy corrosion which impairs functionality.	X	—
Sealing ⁽⁴⁾	Subjected to a depth of 2m for 14 days.		No water penetration into the connector.	X	—
Air tightness ⁽⁴⁾	17.6 kPa of air pressure applied to the inside of the mated connector for 30s.		No air bubbles emitted from the inside of the connector.	X	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
	4	DIS-C-00003790	HT.ZENBA	HY.KOBAYASHI	20200130
REMARK 			APPROVED	SU.OBARA	20120620
Notes (1) Above specifications shows the values in assembled condition with applicable crimp contacts.(Applicable crimp contact:HR41-SC-151) (2) Include temperature rise caused by current-carrying. (3) R/T : Room temperature. (4) Corrosion salt mist, sealing and airtightness shall be tested under mated condition with an applicable connector.			CHECKED	HY.KOBAYASHI	20120620
			DESIGNED	TY.SUZUKI	20120620
			DRAWN	TY.SUZUKI	20120620
Unless otherwise specified, refer to IEC 60512 (JIS C 5402).					
Note	QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC4-117698-00	
	SPECIFICATION SHEET		PART NO.	HR41-25WBP-5SC	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL141-0009-9-00	 1/1