








Notes.

- 1 Co-planarity is within 0.1 mm.
2. As for part No.4 the performance remains good though there might be a difference in the plating luster between each plating lots.
- 3 Per reel : 450 pcs.
The vacuum cap(part No.5) is attached to this product at delivery.
- 4 Refer to the mated condition diagram for the panel thickness and layout.
5. This product is mounted by reflow soldering.
Refer to specification sheet ELC-129413-01-00 for reflow soldering.




3	Stainless Steel		7	PET 	
2	PA	Gray, UL94V-0	6	PS	
1	Copper Alloy	Contact area : Palladium-Nickel 0.75μm+Gold 0.05μm min.	5	PA	Black, UL94V-0
		Lead area : Gold 0.03μm min. Under plating : Nickel 1.27μm min.	4	Stainless Steel	Surface : Tin 1μm min. Under plating : Nickel 0.2μm min.
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS

UNITS mm		SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
		5 : 1	 5	DIS-E-00011281	SN. TOYOSHIMA	KI. KAGOTANI	2022. 10. 0


 HIROSE ELECTRIC CO., LTD.	APPROVED : KI. NAGANUMA	2018. 06. 28	DRAWING NO.	EDC-129413-01-00
	CHECKED : KI. NAGANUMA	2018. 06. 28	PART NO.	IX80G-B-10P (01)
	DESIGNED : YS. SAKODA	2018. 06. 28	CODE NO.	CL0251-0019-0-01
	DRAWN : YS. SAKODA	2018. 06. 28		




May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



HRS	DRAWING NO.	EDC-129413-01-00
	PART NO.	IX80G-B-10P (01)
	CODE NO.	CL0251-0019-0-01