



Designing and Handling Guideline for CX90MW6-16P

Table of contents

1.	Revision History	3
2.	Introduction	
2.1	Purpose	3
2.2	Scope	3
2.3	Reference Specification	3
3.	Product Information	
3.1	Product Feature	4
3.2	Specification	4
3.3	Product Size	5
3.4	Pin Assignment	5
3.5	Manufacturing Date Code System	6
3.6	Part List	7
3.7	Configuration of Product Name	7
3.8	Reel Dimensions	8
3.9	Emboss Carrier Tape Dimensions	8
3.10	Packing Quantity	8
3.11	Peeling Strength	8
3.12	Product Dimension	9
4.	Notice for Soldering	
4.1	Recommended Reflow Temperature Profile	10
4.2	PCB Designing	11
4.3	PIP (Place In Paste)	11
4.4	Metal Mask Designing	12
4.5	Solder Paste	12
5.	Waterproof mechanism	
5.1	Connector with a Gasket	13
5.2	Recommended dimensions of the device chassi	13
5.3	Recommended compression condition of a Gasket	13
6.	Notice for Connector Handling	
6.1	Mating plug	14
6.2	Recommended screw	14

1. Revision History

Revision History	Description of Revisions	Handled by	Date	Remarks
0.1	Draft version	Y.B.PARK	Aug., 05, 2021	-
1.0	Released drawing(RE-2-2139)	Y.B.PARK	Feb., 02, 2023	-
1.1	Released drawing(RE-2-2149)	Y.G.KIM	Feb., 16, 2023	-
1.2	Released drawing(RE-2-2164)	Y.G.KIM	Feb., 28, 2023	-

2. Introduction

2.1 Purpose

The guidelines are intended to provide information on product features and how to handle them.

Guidelines are intended to provide general information and do not limit your design or guarantee results in all situations.

2.2 Scope

Guidelines describe basic design information, recommended device dimensions, and regulatory requirements.

These guidelines will be revised from time to time to reflect changes in technology and production capacity.

2.3 Reference Specification

- Universal Serial Bus Type-C Cable and Connector Specification

Revision 2.1 May 2021

3. Product Information

3.1 Product Feature

- 1) Waterproof type USB Type-C Connector
 - * Meet the requirements of the IPX8 standard
- 2) 6A current rating for quick charging.
- 3) USB 2.0 High-speed(480Mbps) transmission.
- 4) Improved peeling strength using 6 THR* mounting posts.
 - * Through-Hole-Reflow
- 5) Reversible plug orientation ensures easy insertion.
- 6) Compliant to USB specification (USB Type-C compliant interface connector)



3.2 Specification

No. of Contacts	16
P.C.B Mounting type	Mid-Mount
Soldering type	Single row SMT
Current rating	DC 1.5A Max. for each power pin (i.e. A1, A4, A9, A12, B1, B4, B5, B9, B12) DC 0.25 A for the other pins
Voltage rating	48V AC/DC
Operating Temperature	-40°C ~ +105°C (Including Temp.rise), 95% RH MAX
Storage Condition	-10°C ~ +60°C (With Packing), 15% ~ 70% RH
Contact Resistance	40mΩ Max. (Initial)
Withstanding Voltage	100V AC for 1 minute
Insulation Resistance	100MΩ Min. (500V DC)
Mating Cycles	10,000 times
Insertion/ Extraction Force	Insertion: 5~20N, Extraction: 8~20N (Initial), 6~20N (After test)

Note


- * Storage conditions apply to original packaging only, void if opened. Warranty period is 12month max. in the storage conditions above and calculated by manufacture date code.

3.3 Product Size




Width	15.92
Length	7.73
Height	3.56
Center Height	0.131



3.4 Pin Assignment



A1			A4	A5	A6	A7	A8	A9			A12
GND			Vbus	CC1	D+	D-	SBU1	Vbus			GND
GND			Vbus	SBU2	D-	D+	CC2	Vbus			GND
B12			B9	B8	B7	B6	B5	B4			B1




Detail A



Detail B


3.5 Manufacturing Date Code System



Maker		Year		Month		Day		Production Line	
Ex.	Mark	Ex.	Mark	Ex.	Mark	Ex.	Mark	Ex.	Mark
Hirose Korea	H	2020	0	Jan.	1	1st	01	SAMPLE	S
		2021	1	Feb.	2	2nd	02	Manual #1	1
		2022	2	Mar.	3	3rd	03	Manual #2	2
		2023	3	Apr.	4	4th	04	Manual #3	3
		2024	4	May	5	5th	05	Manual #4	4
		2025	5	Jun.	6	6th	06	...	...
		2026	6	Jul.	7	7th	07	Auto #1	A
		2027	7	Aug.	8	8th	08	Auto #2	B
		2028	8	Sep.	9	9th	09	Auto #3	C
		2029	9	Oct.	A	10th	10	Auto #4	D
		2030	0	Nov.	B	11th	11	Auto #5	E
		...	...	Dec.	C	...	...	...	...

3.6 Part List

No	Part	Materials	Finish / Color
1	Insulator	Thermo Plastic	UL94V-0, Black Color
2	Contact	Copper Alloy	Contact, Lead Area : Gold over Nickel plated Non-Contact Area : Nickel plated
3	Mid plate	Stainless Steel	Nickel plated
4	Hold plate	Stainless Steel	Cleansing
5	Main shell	Stainless Steel	Cleansing
6	Lower shell	Stainless Steel	Nickel plated
7	Upper shell	Stainless Steel	Nickel plated
8	Potting	Silicone	Black Color
9	Gasket	Silicone	Gray Color
10	Bonding	Silicone	Black Color




3.7 Configuration of Product Name


CX 90 M W 6 - 16 P
 ① ② ③ ④ ⑤ ⑥ ⑦

①	Series Name	CX	CX Series
②	Soldering Type	90	Right angle SMT
③	Mounting Type	M	Mid-mount
④	Special specifications	W	Waterproof
⑤	Serial No	6	None or 1,2,3...
⑥	Contact No	16	16 position
⑦	Contact Type	P	Male contacts

3.8 Reel Dimensions



3.9 Emboss Carrier Tape Dimensions




※ Emboss Tape was designed in accordance with EIA-481

3.10 Packing Quantity Per Reel: 1,500 PCS

3.11 Peeling Strength:

Cover tape shall have a total peel strength of from 0.3N to 1.0N

3.12 Product Dimensions




Note

- * Specifications herein are subjected to change without notice. Please see the latest drawing to confirm the detail.

4. Notice for Soldering

4.1 Recommended Reflow Temperature Profile




- Profile measuring point
The temperature profile indicates the board surface temperature at the point of contacts with the connector terminals.
- Reflow cycles
Up to 2 cycles of reflow soldering are possible under the same conditions.
* Temperature between 1st and 2nd reflow must be cooled down to room temperature.
- Reflow heating method and condition
Far-infrared heater and hot convective blowers used in combination, normal atmosphere, or nitrogen atmosphere.
- Top surface of the contact leads may not be covered by solder depending on reflow condition.

4.2 PCB Designing


RECOMMENDED PCB LAYOUT (TOP-VIEW)

(REFERENCE ONLY)



4.3 PCB Thickness

Recommended PCB thickness is 0.6 ± 0.05 mm considering 0.45 ± 0.1 mm of PIP leg length.



SECTION A-A	
SECTION B-B	


Section A-A

Section B-B

The PIP leg can be protruded to the bottom side of PCB in case the PCB thickness is less than the PIP leg length.

4.4 Metal Mask Designing

RECOMMENDED METAL MASK LAYOUT (TOP-VIEW)



Note


- * Recommended metal mask thickness is 0.1mm. Above metal mask dimensions are suggested based on 0.6mm of PCB thickness. Please adjust the metal mask opening size in case of thicker PCB than recommended because the lack of solder amount at the PIP holes can be happened.

4.5 Solder Paste


Lead-free solder paste

5. Set Chassis Design Guide


5.1 Connector with a Gasket




5.2 Recommended dimensions of the device chassis



5.3 Recommended compression condition of a Gasket




Detail C



6. Notice for Connector Handling

6.1 Mating Plug

Please use USB Type-C Plug only.



6.2 Recommended Screw

The recommended Screw size is M1.4.

