


Nov.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- △ Note 1. Applicable wire : 26 to 30 AWG
Outer diameter : $\phi 0.56$ to 1.0mm
2. 1 reel:20000 contacts.
- △ ③ Style of reel and box are shown in figure.
- △ 4. A maximum of 5 reels are packed up in one box.
- △ 5. Please be sure to check the form of crimping using a cable when you adjust applicator.
- △ 6. Refer to the technical specification(ATAP-H0373-00)for the packing type.
- △ 7. Refer to the crimping quality standard(ETAD-H0953-00)for the packing type.

Detail of part No. label

HRS		検査
品名コード	CL536-0298-5-41	
品名	DF13-2630SCFA(41)	
数量	20000	
仕様		
LOT No.		
雜ざ目		

Section
Lot No.
Specification
Quantity
Part No.
Code No.

Inspection

NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
1	Phosphor bronze	Contact area:Gold plating 0.2 μ m min Others:Nickel plating 0.5 μ m min			

UNITS	SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	20: 1	8	DIS-H-00004839	HT. SATO	SZ. ONO	20190513

HRS	HIROSE ELECTRIC CO., LTD.	APPROVED : TY. OMA	20060912	DRAWING NO.	EDC-071220-41-01	
		CHECKED : HK. UMEHARA	20060912	PART NO.	DF13-2630SCFA(41)	
		DESIGNED : TS. KUMAZAWA	20060907	CODE NO.	CL536-0298-5-41	
		DRAWN : AK. MIURA	20060906			