



Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
本製品を車載用途などの高い信頼性が求められる機器にご使用の場合は、弊社までお問合せ下さい。












推奨パターン（４：１）



D－D



ソケット嵌合図



注 1 リード平坦度は、金具を含めて０．１mm以内。
2 ////// の範囲にパターン及びバイヤーホールがある場合、
コネクタの端子とショートする可能性があります。

製　品　名	極数	製　品　コ　ー　ド	A	B	C
DF13EA-10DP-1.25V(52)	10	CL536-0570-0-52	12.10	5.00	8.70
DF13EA-20DP-1.25V(52)	20	CL536-0571-0-52	18.35	11.25	14.95
DF13EA-30DP-1.25V(52)	30	CL536-0572-0-52	24.60	17.50	21.20
DF13EA-40DP-1.25V(52)	40	CL536-0573-0-52	30.85	23.75	27.45

NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
2	黄銅	接触部:金めっき 0.2μm min リード部：すずめっき 1μm min 下地:ニッケルめっき 1μm min	6	ポリアミド樹脂	Beige, UL94V-0
			5	ポリエステル	透明, カバーテープ
			4	PS	透明, エンボステープ
1	ポリアミド樹脂	Beige, UL94V-0	3	りん青銅	すずめっき 1μm min

UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	5 : 1	1	1	DIS-H-00016944	HT.SATO	SZ.ONO	20230130


HIROSE ELECTRIC CO., LTD.


APPROVED	HS.OKAWA	20200313
CHECKED	TS.KUMAZAWA	20200313
DESIGNED	HK.HAYASHI	20200313
DRAWN	DS.HIROWATARI	20200306

DRAWING NO. ADC-367982-52-00
PART NO. DF13EA-*DP-1.25V(52)
CODE NO. CL536- 1 1/2

HRS DRAWING FOR REFERENCE


Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
本製品を車載用途などの高い信頼性が求められる機器にご使用の場合は、弊社までお問合せ下さい。






製 品 名	製 品 コ ー ド	極 数	E	F	G	H
DF13EA-10DP-1.25V(52)	CL536-0570-0-52	10	11.5	−	24	24.4
DF13EA-20DP-1.25V(52)	CL536-0571-0-52	20	14.2	28.4	32	32.4
DF13EA-30DP-1.25V(52)	CL536-0572-0-52	30	20.2	40.4	44	44.4
DF13EA-40DP-1.25V(52)	CL536-0573-0-52	40	20.2	40.4	44	44.4

納入時のリール形状（FREE）




注3　1RL　1000個梱包．
　4　引き出し始め30BOXと終わり20BOXに空部があります．
5 L部スプロケット穴は、幅32mm以上のテープに設けます．
6 吸着用キャップは、10，30芯の時製品の中央に（図中、実線部）、
　20，40芯の時ヒロセマーク側に半ピッチずれた位置（図中、点線部）があります．

L部拡大図（10：1）



M−M



品名ラベル詳細

生産日	年　月　日
図番	CL536−＊＊＊＊−＊−52
品名	DF13EA−＊DP−1.25V(52)
納入数量	1000個
納入者	ヒロセ電機株式会社

HRS DRAWING FOR REFERENCE

HRS	DRAWING NO.	ADC-367982-52-00
	PART NO.	DF13EA-＊DP-1.25V(52)
	CODE NO.	CL536-
		1 2/2