

TO
□
□
□
□

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-30 °C TO +85 °C (NOTE1)	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C
	VOLTAGE	250 V AC	APPLICABLE CONTACT	—
	CURRENT	24AWG 3A	APPLICABLE CONNECTOR	DF3-*S-2C
		26AWG 2A	APPLICABLE CABLE	UL1061, 1007:AWG24~28
	28AWG 1A			

SPECIFICATIONS						
ITEM	TEST METHOD	REQUIREMENTS	QT	AT		
CONSTRUCTION						
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	×	×		
MARKING	CONFIRMED VISUALLY.		×	×		
ELECTRICAL CHARACTERISTICS						
CONTACT RESISTANCE	100 mA (DC OR 1000 Hz).	30 mΩ MAX.	×	—		
MECHANICAL CHARACTERISTICS						
CONTACT INSERTION AND EXTRACTION FORCES	□ 0.5±0.002 BY STEEL GAUGE.	INSERTION FORCE 4.4 N MAX. EXTRACTION FORCE 0.3 N MIN.	×	—		
MECHANICAL OPERATION	50 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	×	—		
VIBRATION	FREQUENCY 10 TO 55Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μs.	×	—		
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	② NO DAMAGE, CRACK OR LOOSENESS OF PARTS	×	—		
ENVIRONMENTAL CHARACTERISTICS						
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 → 5~35 → +85 → 5~35 °C TIME 30 → 5~15 → 30 → 5~15 min UNDER 5CYCLES.	① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	×	—		
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, 90~95 %, 96 h.		×	—		
REMARKS NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT.		DRAWN Y.Nagashima	DESIGNED F.Asai	CHECKED T.Miyajima	APPROVED K.Katayama	RELEASED
Unless otherwise specified, refer to MIL-STD-1344.		'01.01.16	01.01.17	01.1.17	'01.1.19	
Note QT:Qualification Test AT:Assurance Test ×:Applicable Test						
HS LTD. HIROSE ELECTRIC CO.,		SPECIFICATION SHEET		PART NO. DF3-2428SCFC		
CODE NO.(OLD) CL	DRAWING NO. ELC4-020356	CODE NO. CL543-0046-0		1/1		