



USER GUIDE for CX90BW1-24P

Table of contents

1.	Revision History	3
2.	Introduction	
2.1	Purpose	3
2.2	Scope	3
2.3	Reference Specification	3
3.	Product Information	
3.1	Product Feature	4
3.2	Specification	4
3.3	Product Size	5
3.4	Pin Assignment	5
3.5	Manufacturing Date Code System	6
3.6	Part List	7
3.7	Configuration of Product Name	7
3.8	Reel Dimensions	8
3.9	Emboss Carrier Tape Dimensions	8
3.10	Packing Quantity	8
3.11	Peeling Strength	8
3.12	Product Dimension	9
4.	Notice for Soldering	
4.1	Recommended Reflow Temperature Profile	10
4.2	PCB Designing	11
4.3	PIP (Place In Paste)	11
4.4	Metal Mask Designing	12
4.5	Solder Paste	12
5.	Water-resistant mechanism	
5.1	Connector with a Gasket	13
5.2	Recommended dimensions of the device chassis	13
5.3	Recommended compression condition of a Gasket	13
6.	Notice for Connector Handling	
6.1	Mating plug	14

1. Revision History

Revision	Date	Handled by	Description of revisions
0.1	Jan., 10, 2024	Y.G.KIM	Draft version release.

2. Introduction

2.1 Purpose

The guidelines are intended to provide information on product features and how to handle them.

Guidelines are intended to provide general information and do not limit your design or guarantee results in all situations.

2.2 Scope

Guidelines describe basic design information, recommended device dimensions, and regulatory requirements.

These guidelines will be revised from time to time to reflect changes in technology and production capacity.□

2.3 Reference Specification

- Universal Serial Bus Type-C Cable and Connector Specification
Revision 2.1 May 2021

3. Product Information

3.1 Product Feature

- 1) Water-resistant type USB Type-C Connector
 - * Meet the requirements of the IPX4 or IPX8 standard
- 2) 5A current rating for quick charging.
- 3) USB4 Gen2x2 (10Gbps x2) transmission.
- 4) Improved peeling strength using 4 THR* mounting posts.
 - * Through-Hole-Reflow
- 5) Reversible plug orientation ensures easy insertion.


3.2 Specification

No. of Contacts	24
P.C.B Mounting type	Top-Mount
Soldering type	Dual row SMT
Current rating	1.25A Max. for each power pin(A1, A4, A9, A12, B1, B4, B9, B12), 1.25A Max. Vconn(i.e. B5) 0.25A for the other pins
Voltage rating	48V AC/DC
Operating Temperature	-40°C ~ +105°C (Including Temp.rise), 95% RH MAX
Storage Condition	-10°C ~ +60°C (With Packing), 15% ~ 70% RH
Contact Resistance	40mΩ Max. (Initial)
Withstanding Voltage	100V AC for 1 minute
Insulation Resistance	100MΩ Min. (500V DC)
Mating Cycles	10,000 times
Insertion/ Extraction Force	Insertion: 5~20N, Extraction: 8~20N (Initial), 6~20N (After test)


Note

- * Storage conditions apply to original packaging only, void if opened. Warranty period is 12month max. in the storage conditions above and calculated by manufacture date



3.3 Product Size




Width	10.50
Length	8.00
Height	3.85
Center Height	1.925




3.4 Pin Assignment



Pin No.	A12	A11	A10	A9	A8	A7	A6	A5	A4	A3	A2	A1
	GND	RX2+	RX2-	Vbus	SBU1	D-	D+	CC	Vbus	TX1-	TX1+	GND
Pin No.	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12
	GND	TX2+	TX2-	Vbus	Vconn	D+	D-	SBU2	Vbus	RX1-	RX1+	GND




Detail A



Detail B


3.5 Manufacturing Date Code System



Year		Month		Day		Production Line	
Ex.	Mark	Ex.	Mark	Ex.	Mark	Ex.	Mark
2020	0	Jan.	1	1st	01	SAMPLE	S
2021	1	Feb.	2	2nd	02	Manual #1	1
2022	2	Mar.	3	3rd	03	Manual #2	2
2023	3	Apr.	4	4th	04	Manual #3	3
2024	4	May	5	5th	05	Manual #4	4
2025	5	Jun.	6	6th	06	...	...
2026	6	Jul.	7	7th	07	Auto #1	A
2027	7	Aug.	8	8th	08	Auto #2	B
2028	8	Sep.	9	9th	09	Auto #3	C
2029	9	Oct.	A	10th	10	Auto #4	D
2030	0	Nov.	B	11th	11	Auto #5	E
...	...	Dec.	C	...	...	...	...

3.6 Part List

No	Part	Materials	Finish / Color
1	INSERT CASE	Thermoplastic	UL94V-0, Black Color
2	CONTACT	Copper Alloy	Contact, Lead Area : Gold over Nickel plated Non-Contact Area : Nickel plated
3	MID PLATE	Stainless Steel	Lead Area : Gold over Nickel plated Other Area : Nickel plated
4	SHELL	Stainless Steel	Cleansing
5	BRACKET	Stainless Steel	Nickel plated
6	GASKET	Silicone	Gray color




3.7 Configuration of Product Name


CX 90 B W 1 - 24 P *
(1) (2) (3) (4) (5) (6) (7) (8)

①	Series Name	CX	CX Series
②	Soldering Type	90	Right angle SMT
③	Mounting Type	B	Top-mount
④	Special specifications	W	Water-resistant
⑤	Serial No.1	1	None or 1,2,3...
⑥	Contact No	24	24 position
⑦	Contact Type	P	Male contacts
⑧	Serial No. 2	Blank	IP54
		1	IP68

3.8 Reel Dimensions



3.9 Emboss Carrier Tape Dimensions




※ Emboss Tape was designed in accordance with EIA-481

3.10 Packing Quantity Peer Reel: 1,400 PCS

3.11 Peeling Strength:


Cover tape shall have a total peel strength of from 0.1N to 1.3N

3.12 Product Dimensions



4. Notice for Soldering

4.1 Recommended Reflow Temperature Profile




- Profile measuring point
The temperature profile indicates the board surface temperature at the point of contacts with the connector terminals.
- Reflow cycles
Up to 2 cycles of reflow soldering are possible under the same conditions.
* Temperature between 1st and 2nd reflow must be cooled down to room temperature
- Reflow heating method and condition
Far-infrared heater and hot convective blowers used in combination, normal atmosphere, or nitrogen atmosphere.
- Top surface of the contact leads may not covered by solder depending on reflow condition

4.2 PCB Designing


RECOMMENDED PCB LAYOUT (TOP-VIEW)

(REFERENCE ONLY)




4.3 PCB Thickness

Recommended PCB thickness is 0.80 ± 0.05 mm considering 0.65 ± 0.1 mm of THR length.



4.4 Metal Mask Designing

RECOMMENDED METAL MASK LAYOUT (TOP-VIEW)



Note


- * Recommended metal mask thickness is 0.1mm. Above metal mask dimensions are suggested based on 0.8mm of PCB thickness. Please adjust the metal mask opening size in case of thicker PCB than recommended because the lack of solder amount at the PIP holes can be happened.

4.5 Solder Paste


Lead-free solder paste

5. Set Chassis Design Guide


5.1 Connector with a Gasket



5.2 Recommended dimensions of the device chassis








5.3 Recommended compression condition of a Gasket



6. Notice for Connector Handling

6.1 Mating Plug

Please use USB Type-C Plug only

With USB Type-C Plug	With the other Plugs
	
 Type A   Type B   Mini-A   Mini-B   Micro-A   Micro-B 	