

圧着条件表

Crimp Condition Table

文書番号 Document No.		ETAD-H1173-00
Approved	SJ.OKAMURA	20240419
Checked	SZ.ONO	20240419
Charged	KI.SUGAWARA	20240419
Drawn	KI.SUGAWARA	20240419

Rev.	0
Dis No.	
Charged	
Checked	
Date	

当社の圧着端子に圧着使用される指定の電線は所定の圧着性能を得る為に、圧着品質基準書を満たすよう作業を実施し、クリンプハイトを次ページの通りに設定し管理願います。
Please control the crimp conditions shown next page for securing the specified performance. Please also do crimping based on the crimp quality standards.

■ 注意事項

- クリンプハイト設定値を外れた場合は品質上の重大な事故となる可能性が有ります。クリンプハイトは品質を決める重要な要点の一つです。
- クリンプハイトの調整方法及び測定方法は、取扱説明書を参照して下さい。
なお、被覆側のクリンプハイトは、電線メーカー、ロットの違い等により特定出来ない場合が有ります。
- 弊社では、芯線側クリンプハイトの最適値を精度よく設定する為に電線毎に試験を実施してクリンプハイトの設定をする事を原則としています。
上記以外の新たな電線のクリンプハイトの設定値につきましては、弊社営業本部までご連絡下さい。
- 本圧着条件表は、弊社純正アプリケーションを使用した場合に限り適用します。
- 圧着条件は予告なく追加される場合があります。
- UL File No.が同じ、かつ芯線構成・芯線めっきが同等の電線については、メーカー名によらず同等の圧着条件で圧着可能です。

■ Notice

- Controlling the crimp height is an important task to decide the quality of the crimping.
It may lead to a serious quality problem if the crimp height is not properly established.
- Please refer to an instruction manual for the method of adjustment and measurement of the crimp height.
The crimp height shown on the wire insulators will, in many case,
be for reference only as they will differ per each cable manufacturer and the production volume.
- Hirose's internal rule is to establish a crimp height by performing a crimp testing on every wire in order to provide a precise crimp height strictly.
As such, it is recommended that our sales representative are consulted, if any other wires are to be used besides these.
- The crimp condition table is applied only if the tool specified by Hirose is used.
- The crimp condition table is subject to be added without notice.
- The wire which UL File No., its conductor construction and conductor plating are same can be crimped with same crimp condition even if the wire manufacturer is different.

■ 特記事項 / Other items of note

圧着条件表
Crimp Condition Table

適用圧着端子 Applicable Crimp Contact		圧着品質基準書 Applicable Crimp Quality Standards
HRS No.	製品名 Product name	
0543-0615-4-00	DF11-EP2428PCF	

文書番号		ETAD-H1173-00
Approved	SJ.OKAMURA	20240419
Checked	SZ.ONO	20240419
Charged	KI.SUGAWARA	20240419
Drawn	KI.SUGAWARA	20240419

Rev.	0
Dis No.	
Charged	
Checked	
Date	

No.	標準条件 Recommended	UL No./ Cable Name	AWG size	メーカー名 Manufacture	芯線構成 Construction	芯線めっき Plating	芯線材質 Conductor Material	被覆外径 Insulator dia	被覆材質 Insulator Material	芯線部クリンプハイト Conductor Crimp Height		芯線部クリンプワイド Conductor Crimp Width		被覆部クリンプハイト Insulator Crimp Height		被覆部クリンプワイド Insulator Crimp Width		圧着部強度MIN Minimum Crimp Barrel Tensile strength [N]	適合アプリケーション Applicable tool
										MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX		
AA	○	1061	24	-	11/0.16	Sn	軟銅線 Copper-wire	1.10	PVC	0.66	0.72	-	-	1.40	1.55	-	-	35	AP105-DF11-EP2428P
AB	○	1061	26	-	7/0.16	Sn	軟銅線 Copper-wire	1.00	PVC	0.60	0.66	-	-	1.35	1.50	-	-	24	AP105-DF11-EP2428P
AC	○	1061	28	-	7/0.127	Sn	軟銅線 Copper-wire	0.90	PVC	0.56	0.62	-	-	1.30	1.45	-	-	16	AP105-DF11-EP2428P
AD		1095	24	-	11/0.16	Sn	軟銅線 Copper-wire	1.30	PVC	0.66	0.72	-	-	1.50	1.65	-	-	35	AP105-DF11-EP2428P
AE		1095	26	-	7/0.16	Sn	軟銅線 Copper-wire	1.20	PVC	0.60	0.66	-	-	1.45	1.60	-	-	24	AP105-DF11-EP2428P
AF		1095	28	-	7/0.127	Sn	軟銅線 Copper-wire	1.10	PVC	0.56	0.62	-	-	1.40	1.55	-	-	16	AP105-DF11-EP2428P
AG	○	1007	24	-	11/0.16	Sn	軟銅線 Copper-wire	1.40	PVC	0.66	0.72	-	-	1.55	1.65	-	-	35	AP105-DF11-EP2428P
AH	○	1007	26	-	7/0.16	Sn	軟銅線 Copper-wire	1.30	PVC	0.60	0.66	-	-	1.50	1.65	-	-	24	AP105-DF11-EP2428P
AI	○	1007	28	-	7/0.127	Sn	軟銅線 Copper-wire	1.20	PVC	0.56	0.62	-	-	1.45	1.60	-	-	16	AP105-DF11-EP2428P
AJ		1571	24	-	11/0.16	Sn	軟銅線 Copper-wire	1.00	PVC	0.66	0.72	-	-	1.35	1.50	-	-	35	AP105-DF11-EP2428P
AK		1571	26	-	7/0.16	Sn	軟銅線 Copper-wire	0.90	PVC	0.60	0.66	-	-	1.30	1.45	-	-	24	AP105-DF11-EP2428P
AL		1571	28	-	7/0.127	Sn	軟銅線 Copper-wire	0.80	PVC	0.56	0.62	-	-	1.25	1.40	-	-	16	AP105-DF11-EP2428P
AM		1569	24	LTK	11/0.16	Sn	軟銅線 Copper-wire	1.43	PVC	0.66	0.72	-	-	1.55	1.65	-	-	35	AP105-DF11-EP2428P
AN																			
AO																			
AP																			
AQ																			
AR																			