







Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




- NOTES 1. The dimension in parentheses are for reference.
2. Lead CO-PLANARITY shall be 0.1 MAX.
3. See dimension table in the appendix.
4. This product satisfies halogen free requirements defined as 900ppm maximum chlorine, 900ppm maximum bromine, and 1500ppm maximum total of chlorine and bromine.
5. 'n' represents the number of contacts.
6. See dimension table in the appendix.

4	PHOSPHOR BRONZE	(CONTACT AREA: LEAD) GOLD PLATING 0.05μm MIN. OVER NICKEL 1μm MIN. (OTHER) NICKEL 1μm MIN.			
3	PHOSPHOR BRONZE	(CONTACT AREA: LEAD) GOLD PLATING 0.05μm MIN. OVER NICKEL 1μm MIN. (OTHER) NICKEL 1μm MIN.	8	(CONNECTOR)	
2	LCP	(BLACK)	UL94V-0	6	POLYESTER
1	LCP	(BEIGE)	UL94V-0	5	POLYSTYRENE
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 5 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED CHECKED DATE
HIROSE ELECTRIC CO., LTD.		APPROVED : NF. MIYAZAKI	16.10.28	DRAWING NO.	EDC-349783-00-00
		CHECKED : YH. MICHIDA	16.10.28	PART NO.	FH40-**S-0.5SV(99)
		DESIGNED : RT. IKEDA	16.10.28	CODE NO.	CL580
		DRAWN : RK. OGASAWARA	16.10.28		







Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

PART NO.	CODE NO.	NUMBER OF CONTACT	DIMENSION OF CONNECTOR, PCB MOUNTING PATTERN, STENCIL PATTERN AND FFC/FPC					DIMENSION OF DRAWING FOR PACKING						
			A	B	C	D	E	F	G	H	J	K	L	M
FH40-10S-0.5SV(99)	CL580-2104-6-99	10	5.57	8.2	4.5	5.5	7.1	16	—	7.5	8.4	5.2	17.4	21.4
FH40-20S-0.5SV(99)	CL580-2105-9-99	20	10.57	13.2	9.5	10.5	12.1	24	—	11.5	13.4	10.2	25.4	29.4
FH40-24S-0.5SV(99)	CL580-2106-1-99	24	12.57	15.2	11.5	12.5	14.1	24	—	11.5	15.4	12.2	25.4	29.4
FH40-30S-0.5SV(99)	CL580-2108-7-99	30	15.57	18.2	14.5	15.5	17.1	32	28.4	14.2	18.4	15.2	33.4	37.4
FH40-40S-0.5SV(99)	CL580-2107-4-99	40	20.57	23.2	19.5	20.5	22.1	44	40.4	20.2	23.4	20.2	45.4	49.4
FH40-45S-0.5SV(99)	CL580-2101-8-99	45	23.07	25.7	22.5	23	24.6	44	40.4	20.2	25.9	22.7	45.4	49.4
FH40-50S-0.5SV(99)	CL580-2100-5-99	50	25.57	28.2	24.5	25.5	27.1	44	40.4	20.2	28.4	25.2	45.4	49.4
FH40-60S-0.5SV(99)	CL580-2109-0-99	60	30.57	33.2	29.5	30.5	32.1	56	52.4	26.2	33.4	30.2	57.4	61.4
FH40-64S-0.5SV(99)	CL580-2102-0-99	64	32.57	35.2	31.5	32.5	34.1	56	52.4	26.2	35.4	32.2	57.4	61.4
FH40-80S-0.5SV(99)	CL580-2103-3-99	80	40.57	43.2	39.5	40.5	42.1	56	52.4	26.2	43.4	40.2	57.4	61.4

HRS	DRAWING NO.	EDC-349783-00-00		
	PART NO.	FH40-**S-0.5SV(99)		
	CODE NO.	CL580		5