

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO 105 °C(note1)	STORAGE TEMPERATURE RANGE	-10 °C TO 50 °C (PACKED CONDITION)	
	VOLTAGE	50 V AC / DC	OPERATING OR STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 90 % MAX (NOT DEWED)	
	CURRENT	0.5 A (note2)	APPLICABLE CABLE	t=0.3±0.05mm, GOLD PLATING	
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	QT AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X X
MARKING		CONFIRMED VISUALLY.			X X
ELECTRICAL CHARACTERISTICS					
CONTACT RESISTANCE		AC 20 mV MAX (1 KHz) , 1 mA .		50 mΩ MAX. INCLUDING FPC, FFC BULK RESISTANCE (L=8mm)	X X
INSULATION RESISTANCE		100 V DC.		500 MΩ MIN.	X X
VOLTAGE PROOF		150 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	X X
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION		20 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —
VIBRATION		FREQUENCY 10 TO 55 Hz, HALF AMPLITUDE 0.75 mm, — m/s ² FOR 10 CYCLES IN 3 AXIAL DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② CONTACT RESISTANCE: 50 mΩ MAX.	X —
SHOCK		981 m/s ² , DURATION OF PULSE 6 ms AT 3 TIMES IN 3 BOTH AXIAL DIRECTIONS.		③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —
FPC RETENTION FORCE		MEASURED BY APPLICABLE FPC. (THICKNESS OF FPC SHALL BE t=0.30mm AT INITIAL CONDITION.)		DIRECTION OF INSERTION: 0.3N × n MIN. VERTICAL DIRECTION TO INSERTION: 0.2N × n MIN. (n:NUMBER OF CONTACTS)	X —
ENVIRONMENTAL CHARACTERISTICS					
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -40→+15To+35→+105→+15To+35°C TIME 30→ 2 TO 3 → 30→ 2 TO 3 min UNDER 5 CYCLES.		① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE: 50 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2°C, RELATIVE HUMIDITY 90 TO 95 %, 96 h.			X —
DAMP HEAT, CYCLIC		EXPOSED AT -10 TO +65 °C, RELATIVE HUMIDITY 90 TO 96 %, 10 CYCLES, TOTAL 240 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE: 1 MΩ MIN. (AT HIGH HUMIDITY) ③ INSULATION RESISTANCE: 50 MΩ MIN. (AT DRY) ④ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —
DRY HEAT		EXPOSED AT 105±2 °C, 96 h.		① CONTACT RESISTANCE: 50 mΩ MAX.	X —
COLD		EXPOSED AT -40±3°C, 96 h.		② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —
CORROSION SALT MIST		EXPOSED AT 35±2°C , 5 % SALT WATER SPRAY FOR 96 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR.	X —
SULPHUR DIOXIDE [JIS C 60068-2-42]		EXPOSED AT 40±2 °C , RELATIVE HUMIDITY 80±5% , 25±5 ppm FOR 96 h.			X —
HYDROGEN SULPHIDE [JIS C 60068-2-43]		EXPOSED AT 40±2 °C , RELATIVE HUMIDITY 80±5% , 10 TO 15 ppm FOR 96 h.			X —
△	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
REMARK			APPROVED	NF. MIYAZAKI	16.10.28
			CHECKED	YH. MICHIDA	16.10.28
			DESIGNED	RT. IKEDA	16.10.28
Unless otherwise specified, refer to IEC 60512.			DRAWN	RK. OGASAWARA	16.10.28
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-349783-00-00
HRS	SPECIFICATION SHEET		PART NO.	FH40-**S-0. 5SV (99)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL580	△ 1/2

SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING PEAK TMP. 250 °C MAX . REFLOW TMP.OVER 230 °C WITHIN 60 sec. 2) SOLDERING IRONS : TMP. 350±5°C FOR 5±1 sec .	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	x	—	
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 245±5 °C FOR IMMERSION DURATION, 2±0.5 sec.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	x	—	
(note1) FOLLOW THE SPECIFICATIONS OF FPC/FFC IF IT'S ALLOWABLE MAXIMUM OPERATING TEMPERATURE IS BELOW 105°C. (note2) WHEN THE SAME VALUE OF CURRENT ARE APPLID TO ALL CONTACTS AT THE SAME TIME IN ONCE, SET THE CURRENT TO THE 70 % OF THE RATED CURRENT VALUE.					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC-349783-00-00		
	SPECIFICATION SHEET	PART NO.	FH40-**S-0. 5SV (99)		
	HIROSE ELECTRIC CO., LTD.	CODE NO	CL580		2/2