

Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

	COUNT	DESCRIPTION OF REVISIONS	BY	CHECKED	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHECKED	DATE
△						△					
△						△					
APPLICABLE STANDARD											
RATING	ELECTRIC SOURCE	PHASE	AC-DC	V	Hz	WEIGHT		0.5 kg			
	DISSIPATION POWER					APPLICABLE CONNECTOR		DF62-30SCA 544-0528-8 DF62-EP30PCA 544-0531-2 DF62-30SC 544-0574-5 DF62-EP30PC 544-0577-3			
	AIR SOURCE					APPLICABLE CABLE		UL1061 AWG30			
	AIR CONSUMPTION										
	OPERATING TEMPERATURE LIMIT	°C~°C				APPLICABLE EQUIPMENT					
	SPECIFICATIONS										
CONSTITUTION	ITEM	TEST METHOD				REQUIREMENTS		QT	AT		
	APPEARANCE, STRUCTURE AND FINISH	Visually and by measuring instrument.				According to drawing.		○	○		
	MARKING	Confirmed visually.				According to drawing.		○	○		
REMARKS											
						DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED	
						14.6.17 H.KUDO	14.6.17 M.TAKAHASHI	14.6.18 S. Otake	14.6.18 T. Ito		
Unless otherwise specified, refer to											
Note QT:Qualification Test AT:Assurance Test X:Applicable Test											
HRS HIROSE ELECTRIC CO.,LTD.						SPECIFICATION SHEET			PART NO. HT801/DF62-30(10)		
CODE NO. (OLD)				DRAWING NO. ELC4- 276271-10		CODE NO. CL 550-0402-1-10				1 1	

FROM001-1