






Drawing for mating(No scale)



- 1 Lead CO-Planarity is 0.1mm MAX.
 - 2 This is packaged in tray. (50pcs/tray)
 - 3 Blemish and hit mark can be occurred through out the manufacturing process which dosen't affect quality level.
 - 4 Please note that excessive wrenching force could damage this connector. Please refer to the guideline for detailed regulations of the mating method.
 - 5 No prohibited area for printing pattern or via hole. PCB resist can be printed optionally.
 - 6 The dimensions in parentheses are for references.

resist can be printed optionally.
dimensions in parentheses are for references.

			4	BRASS	TIN-PLATING 1 μm
			2.3	PHOSPHOR BRONZE	CONTACT AREA:GOLD 0.1 μm
					LEAD AREA:GOLD 0.03 μm
					UNDER PLATING:NICKEL 1 μm

1	LCP	BLACK UL94V-0
NO.	MATERIAL	FINISH , REMARKS

UNITS mm		SCALE 2 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.	APPROVED : HS. OKAWA		13. 09. 25		DRAWING NO.	EDC3-348431-00		
	CHECKED : KI. HIROKAWA		13. 09. 25		PART NO.	FX20-140S-0.5SH		
	DESIGNED : TS. OONO		13. 09. 25		CODE NO.	CL570-1606-1-00		
	DRAWN : TS. OONO		13. 09. 25		 1/1			