

APPLICABLE STANDARD								
△ RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ^{(1) (2)}		STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽³⁾			
	VOLTAGE	60 V AC ⁽⁵⁾		OPERATING HUMIDITY RANGE	RH 85 % MAX ^{(2) (4)}			
	CURRENT	0.5 A ⁽⁵⁾		STORAGE HUMIDITY RANGE	RH 70 % MAX ^{(3) (4)}			
	APPLICABLE CABLE	AWG 36, 40 THIN COAXIAL CABLE						
SPECIFICATIONS								
ITEM		TEST METHOD		REQUIREMENTS		QT	AT	
CONSTRUCTION								
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		×	×	
MARKING		CONFIRMED VISUALLY.				×	×	
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED		DATE
△	2	DIS-F-004353		KN. SHIBUYA		HT. YAMAGUCHI		09.12.15
REMARKS				APPROVED	HS. OKAWA		08.05.24	
(1) INCLUDE TEMPERATURE RISE CAUSED BY CURRENT-CARRYING. (2) OPERATING TEMPERATURE SHOULD BE -55 TO 40°C WHEN HUMIDITY EXCEEDS 80% RH. (3) THE SPECIFICATION IS APPLIED TO THE PRE-ASSEMBLED COMPONENT AND THE CABLE ASSEMBLED PRODUCT BOTH IN DELIVERY AND STORAGE, BEFORE ASSEMBLED TO PCB. (4) THERE MUST NOT BE DEWFALL. (5) IT IS THE MAXIMUM VALUE OF CONNECTOR. CONFIRM THE SPECIFICATION OF THE CABLE.				CHECKED	HT. YAMAGUCHI		08.05.24	
				DESIGNED	TS. SHIBUYA		08.05.24	
				DRAWN	TS. SHIBUYA		08.05.24	
				Unless otherwise specified, refer to JIS-C-5402.				
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.		ELC4-158279-00		
HRS	SPECIFICATION SHEET			PART NO.		FX16-21P-GNDL		
	HIROSE ELECTRIC CO., LTD.			CODE NO.		CL575-3331-8-00		△