

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO 125 °C	STORAGE TEMPERATURE RANGE	-10 °C TO 50 °C (PACKED CONDITION)	
	VOLTAGE	50 V AC / DC	OPERATING OR STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 90 % MAX (NOT DEWED)	
	CURRENT	0.5 A	APPLICABLE CABLE	t=0.3±0.05mm, GOLD PLATING HEAT RESISTANCE:125°C	
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	QT AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X X
MARKING		CONFIRMED VISUALLY.			X X
ELECTRICAL CHARACTERISTICS					
CONTACT RESISTANCE		AC 20 mV MAX (1 KHz) , 1 mA .		50 mΩ MAX. INCLUDING FPC, FFC BULK RESISTANCE (L=8mm)	X X
INSULATION RESISTANCE		100 V DC.		500 MΩ MIN.	X X
VOLTAGE PROOF		150 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	X X
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION		20 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —
VIBRATION		FREQUENCY 10 TO 55 Hz, HALF AMPLITUDE 0.75 mm, — m/s ² FOR 10 CYCLES IN 3 AXIAL DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② CONTACT RESISTANCE: 50 mΩ MAX.	X —
SHOCK		981 m/s ² , DURATION OF PULSE 6 ms AT 3 TIMES IN 3 BOTH AXIAL DIRECTIONS.		③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —
FPC RETENTION FORCE		MEASURED BY APPLICABLE FPC. (THICKNESS OF FPC SHALL BE t=0.30mm AT INITIAL CONDITION.)		DIRECTION OF INSERTION: 0.4N × n MIN. (n:NUMBER OF CONTACTS) (note 1)	X —
ENVIRONMENTAL CHARACTERISTICS					
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -40→+15T ₀ +35→+125→+15T ₀ +35°C TIME 30→ 2 T ₀ 3 → 30 → 2 T ₀ 3 min UNDER 1000 CYCLES.		① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE: 50 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —
DAMP HEAT (STEADY STATE)		EXPOSED AT 60±2°C, RELATIVE HUMIDITY 90 TO 95 %, 1000 h.			X —
DAMP HEAT,CYCLIC		EXPOSED AT -10 TO +65 °C, RELATIVE HUMIDITY 90 TO 96 %, 10 CYCLES,TOTAL 240 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE: 1 MΩ MIN. (AT HIGH HUMIDITY) ③ INSULATION RESISTANCE: 50 MΩ MIN. (AT DRY) ④ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —
DRY HEAT		EXPOSED AT 125±2 °C, 1000 h.		① CONTACT RESISTANCE: 50 mΩ MAX.	X —
COLD		EXPOSED AT -40±3 °C, 1000 h.		② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —
CORROSION SALT MIST		EXPOSED AT 35±2 °C , 5 % SALT WATER SPRAY FOR 96 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR.	X —
SULPHUR DIOXIDE [JIS C 60068-2-42]		EXPOSED AT 40±2 °C , RELATIVE HUMIDITY 80±5% ,25±5 ppm FOR 96 h.			X —
HYDROGEN SULPHIDE [JIS C 60068-2-43]		EXPOSED AT 40±2 °C , RELATIVE HUMIDITY 80±5% ,10 TO 15 ppm FOR 96 h.			X —
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARK			APPROVED	HS. SAKAMOTO	20200309
			CHECKED	FN. TAMURA	20200309
			DESIGNED	KN. KOBAYASHI	20200306
			DRAWN	NM. YONEYAMA	20200306
Unless otherwise specified, refer to IEC 60512.					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-381457-98-00
HRS	SPECIFICATION SHEET		PART NO.	FH28KH-80S-0. 5SH (98)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL586-1874-0-98	△ 1/2

SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING (MAX 2 CYCLES) PEAK TMP. 250 °C MAX . REFLOW TMP. OVER 230 °C WITHIN 60 sec. PRE-HEAT 150 TO 200°C FOR 90 TO 120 sec. 2) SOLDERING IRONS : TMP. 350±10°C FOR 5±1 sec .	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	x	—	
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 245±3 °C FOR IMMERSION DURATION, 3±0.3 sec.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	x	—	
(note 1) THERE'S A CASE WHICH FPC/FFC RETENTION FORCE DOESN'T FULFILL THE VALUE, BECAUSE FPC/FFC SPECIFICATION AFFECTS THE RESULT OF FPC/FFC RETENTION FORCE.					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC-381457-98-00		
	SPECIFICATION SHEET	PART NO.	FH28KH-80S-0. 5SH (98)		
	HIROSE ELECTRIC CO., LTD.	CODE NO	CL586-1874-0-98		2/2