


Oct.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	Operating temperature range	-55 °C to 85 °C	Storage temperature range	-10°C TO 50°C(Packed condition)
	Voltage	30V AC / DC	Operating or storage humidity range	Relative humidity 90 % MAX(Not dewed)
	Current	 0.3 A	Applicable cable	t=0.3±0.03mm, Gold plating

SPECIFICATIONS


ITEM	TEST METHOD	REQUIREMENTS	QT	AT
------	-------------	--------------	----	----

CONSTRUCTION				
General examination	Visually and by measuring instrument.	According to drawing. (note 1)	×	×
Marking	Confirmed visually.		×	×

ELECTRICAL CHARACTERISTICS				
Voltage proof	90 V AC for 1 min.	No flashover or breakdown.	×	—
Insulation resistance	100 V DC.	50 MΩ MIN.	×	—
Contact resistance	AC 20 mV MAX, 1 mA.	100 mΩ MAX. Including FPC bulk resistance (L=8mm)	×	—

MECHANICAL CHARACTERISTICS				
Vibration	Frequency 10 to 55 Hz, half amplitude 0.75 mm, for 10 cycles in 3 axial directions.	① No electrical discontinuity of 1 μs. ② Contact resistance: 100 mΩ MAX. ③ No damage, crack and looseness of parts.	×	—
Shock	981 m/s ² , duration of pulse 6 ms at 3 times in 3 both axial directions.		×	—
Mechanical operation	10 times insertions and extractions.	① Contact resistance: 100 mΩ MAX. ② No damage, crack and looseness of parts.	×	—
FPC insertion force	Measured by applicable FPC (Thickness of FPC shall be t=0.30mm at initial condition.)		×	—
FPC retention force	Measured by applicable FPC (Thickness of FPC shall be t=0.30mm at initial condition.)	Retention force : Direction of extraction 5+0.07 × n N MIN (note3) (n: Number of contacts)	×	—


ENVIRONMENTAL CHARACTERISTICS				
Corrosion salt mist	Exposed at 35±2 °C, 5 % salt water spray for 96 h.	① Contact resistance: 100 mΩ MAX.	×	—
Rapid change of temperature	Temperature -55→+15T _O +35→+85→+15T _O +35°C Time 30→ 2 to 3 → 30 → 2 to 3 min Under 5 cycles.	① Contact resistance: 100 mΩ MAX. ② Insulation resistance: 50 MΩ MIN. ③ No damage, crack and looseness of parts.	×	—
Damp heat (steady state)	Exposed at 40±2 °C, Relative humidity 90 to 95 %, 96 h.		×	—
Damp heat,cyclic	Exposed at -10 to +65 °C, Relative humidity 90 to 96 %, 10 cycles, TOTAL 240 h.	① Contact resistance: 100 mΩ MAX. ② Insulation resistance: 1 MΩ MIN. (At high humidity) ③ Insulation resistance: 50 MΩ MIN. (At dry) ④ No damage, crack and looseness of parts	×	—

COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 3	DIS-F-00010250	SE. YOKOYAMA	HY. YAMAZAKI	20210713

REMARK	APPROVED	NF. MIYAZAKI	20170404
	CHECKED	YN. TAKASHITA	20170404
	DESIGNED	HH. MURAKAMI	20170404
	DRAWN	HH. MURAKAMI	20170404

Unless otherwise specified, refer to IEC 60512.

Note QT:Qualification Test AT:Assurance Test X:Applicable Test	DRAWING NO.	ELC-368163-10-01
--	-------------	------------------

HRS	SPECIFICATION SHEET	PART NO.	FH62-**S-0. 25SHW (10)	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL580	 1/2

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
Dry heat	Exposed at 85±2°C, 96 h.	① Contact resistance: 100 mΩ MAX.	×	—
Cold	Exposed at -55±3°C, 96 h.	② No damage, crack and looseness of parts	×	—
Sulphur dioxide [JIS C 60068-2-42]	Exposed at 40±2 °C, Relative humidity 80±5% 25±5 ppm for 96 h.	① Contact resistance: 100 mΩ MAX.	×	—
Hydrogen sulphide [JIS C 60068-2-43]	Exposed at 40±2 °C, Relative humidity 80±5% , 10 to 15 ppm for 96 h.		×	—
Solderability	Soldered at solder temperature, 245±3°C for immersion duration,3±0.3 sec.	A new uniform coating of solder shall cover a minimum of 95 % of the surface being immersed.	×	—
Resistance to soldering heat	1) Reflow soldering : Peak TMP. 250 °C MAX . Reflow TMP. over 220 °C 60 to 90 sec. Number of reflow : 2 times 2) Soldering irons : TMP. 350±10 °C for 5±1 sec .	No deformation of case of excessive looseness of the terminals. (<i>note 4</i>)	×	—


(note 1)

This product features top-contact point.
"One Action Lock" completes FPC lock just by inserting the FPC.
Do not operate the locking-lever when inserting the FPC.

(note 2)



Do not insert the FPC to this product at an angle.

(note 3)

 There's a case which FPC retention force doesn't fulfill the value, because FPC specification affects the result of FPC retention force.
Stabilize the FPC to PCB or something fixed, if pull-up or pull-down force is expected to be applied to the FPC.

(note 4)

Blisters which may be generated on the housing do not affect product performance.

Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.		ELC-368163-10-01	
	SPECIFICATION SHEET		PART NO.	FH62-**S-0. 25SHW (10)	
	HIROSE ELECTRIC CO., LTD.		CODE NO	CL580	 2/2