









MATED HIGHT (h)		(mm)
RECEPTACLE NO.	HEADER NO.	
DF17A(3.0)-40DS-0.5V(57)		
DF17#(2.0)-40DP-0.5V(57)		5
DF17#(4.0)-40DP-0.5V(57)		7



RECOMMENDED PATTERN



A-A (10:1)



- NOTES
- 1: LEAD CO-PLANARITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1mm MAX.
 - 2: WHEN A PART MARKED WITH  HAS A PATTERN BUT NO RESIST ON IT. TAKE CARE TO PREVENT THE CONNECTOR FROM TOUCHING IT.

2	POLYAMIDE (PA6T)	WHITE BEIGE . UL94V-0			
1	PHOSPHER BRONZE	CONTACT AREA:GOLD PLATED 0.1µm min LEAD AREA:GOLD PLATED 0.02µm min UNDER PLATING : NICKEL 1µm min	5	PS	BLACK (PLASTIC REEL)
			4	POLYESTER	CLEAR (COVER TAPE)
			3	A-PET	CLEAR (EMBOSSSED CARRIER TAPE)
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 5 : 1	COUNT △		DESCRIPTION OF REVISIONS
DESIGNED		CHECKED		DATE	
APPROVED : KH. IKEDA		08.11.20		DRAWING NO.	
CHECKED : TS. MIYAZAKI		08.11.20		PART NO.	
DESIGNED : TY. YAMASAKI		08.11.19		CODE NO.	
DRAWN : TY. YAMASAKI		08.11.19		CL683-0014-1-57	
HIROSE ELECTRIC CO., LTD.		EDC3-161648-02		DF17A(3.0)-40DS-0.5V(57)	
				1/2	

