








A
B
C
D
E
F




- NOTES 1 LEAD CO-PLANARITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1mm MAX .
2 WHEN A PART MARKED WITH  HAS A PATTERN BUT NO RESIST ON IT.
TAKE CARE TO PREVENT THE CONNECTOR FROM TOUCHING IT.

MATED HIGHT (h)		(mm)	
HEADER NO.	RECEPTACLE NO.	DF17*(3.0)-20DS-0.5V(57)	DF17*(4.0)-20DS-0.5V(57)
DF17B(2.0)-20DP-0.5V(57)	5		6

2	POLYAMIDE (PA6T)	WHITE BEIGE , UL94V-0	6	PS	PLASTIC REEL , BLACK
1	PHOSPHER BRONZE	CONTACT AREA:GOLD PLATED 0.1μm min LEAD AREA:TIN PLATED 1μm min UNDER PLATING:NICKEL PLATED 1μm min	5	POLYESTER	CLEAR (COVER TAPE)
			4	A-PET	CLEAR(EMBOSSD CARRIER TAPE)
			3	PHOSPHER BRONZE	TIN PLATED : 1μm min UNDER PLATING:NICKEL PLATED 1μm min
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 5 : 1	COUNT		DESCRIPTION OF REVISIONS
		APPROVED : KH. IKEDA	08.09.16	DRAWING NO. EDC3-161736-02	
HIROSE ELECTRIC CO., LTD.		CHECED : TS. MIYAZAKI	08.09.16	PART NO. DF17B(2.0)-20DP-0.5V(57)	
		DESIGNED : TY. YAMASAKI	08.08.19	CODE NO. CL683-0102-7-57	
		DRAWN : TY. YAMASAKI	08.08.19	 1/2	

A
B
C
D
E
F

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



HRS	DRAWING NO.	EDC3-161736-02		
	PART NO.	DF17B(2.0)-20DP-0.5V(57)		
	CODE NO.	CL683-0102-7-57	△	2/2