




| Check point                     |    | Measure(mm)     |
|---------------------------------|----|-----------------|
| Cover location.                 | A  | 0. 3 ± 0 1. 3   |
| Location of tip of the core.    | B  | 0. 2 ± 0 1. 3   |
| Bell-mouth.                     | C1 | 0. 2 ± 0 0. 6   |
|                                 | C2 | 0. 1 ± 0 0. 5   |
| Bent-up.                        | D  | 3° MAX          |
| Bent-down.                      | E  | 3° MAX          |
| Twist.                          | F  | ± 3° MAX        |
| Rolling.                        | G  | ± 3° MAX        |
| Cut-off tab.                    | H  | 0. 2 MAX        |
| Strip length prior to crimping. | I  | 2 3. 5 ± 0 4. 5 |
| Height of metal cut-out teeth.  | J  | 0. 1 MAX        |

Note 1 To adjust applicator, please check the crimping condition (Crimping height and configuration) by using cable.  
2 This dimension is for reference, please adjust it to meet specified dimensions after the crimping.

| COUNT                   | DESCRIPTION OF REVISIONS | DESIGNED | CHECKED                       | DATE                   |
|-------------------------|--------------------------|----------|-------------------------------|------------------------|
| 0                       |                          |          |                               |                        |
| TITLE                   |                          |          | HRS HIROSE ELECTRIC CO., LTD. |                        |
| DF22#-1416PCF(A)        |                          |          | APPROVED                      | HS. OKAWA 20181023     |
| Crimp Quality Standard  |                          |          | CHECKED                       | SZ. ONO 20181023       |
|                         |                          |          | CHARGED                       | TO. KUROMATSU 20181023 |
|                         |                          |          | WRITTEN                       | SK. CHIBA 20181023     |
| TECHNICAL SPECIFICATION |                          |          | ETAD-H0952-00                 | 0 1 1                  |