


Applicable standard					
Rating	Operating temperature range	-40 °C to 85 °C	Storage temperature range	-40 °C to 60 °C (At packing)	
Specifications					
Item		Test method	Requirements	QT	AT
Construction					
General examination	Visually and measuring instrument.		According to drawing.	X	X
Marking	Confirmed visually.				
Environmental characteristics					
Salt mist	Salt mist:5% ,Time:48 hours		No heavy corrosion ruins the function.	X	—
Water resistance	Put the product into water at a depth of 1m for 30min. Δ (IP67)		No water intrusion inside the connector Δ	X	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
▲	2	DIS-K-00001873	TY. SATO	TS. YAMAZAKI	20190426
REMARK A product corresponding to RoHS.			APPROVED	MT. SHIBUTANI	20170801
			CHECKED	FS. YOSHIDA	20170801
			DESIGNED	TY. SATO	20170801
			DRAWN	TY. SATO	20170801
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-376694-00-00
	SPECIFICATION SHEET		PART NO.	MF11BMT-WRC2	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL709-7036-0-00	▲ 1/1